



REV.	DATE	DESCRIPTION
A	06/05/03	UPDATE DRAWING FORMAT



NOTES:

- CONTACT PIN TO SOLDER
- MAX. PANEL THICKNESS = 6.8mm

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						06/05/03
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	CHECKED		PART DESCRIPTION					
6	HEX NUT	BRASS	GOLD	1		ISSUED			MCX BULKHEAD DIRECT SOLDER JACK (FOR .085” .086” SEMI RIGID CABLE)				
5	LOCK WASHER	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	SHEET	1 OF 1		PART NO.				
4	INSULATOR	TEFLON	NATURAL	1					252163				
3	CONTACT PIN	BER. COPPER	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1	DO NOT SCALE DRAWING	CAD FILE	C:/252/252163.DWG	DWG. NO.		252163.DWG	REV. A	SIZE A	SCALE NA
1	BODY	BRASS	GOLD	1									
DESCRIPTION		MATERIAL	FINISH	QTY									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[252163](#)