

ULTRA FAST RECTIFIER

VOLTAGE RANGE: 50 --- 600 V

CURRENT: 1.0 A


FEATURES

- ◇ Low cost
- ◇ Diffuse junction
- ◇ Ultra fast switching for high efficiency
- ◇ Low reverse leakage current
- ◇ Low forward voltage drop
- ◇ High current capability
- ◇ The plastic material carries U/L recognition 94V-0

MECHANICAL DATA

- ◇ Case: JEDEC A-405, molded plastic
- ◇ Polarity: Color band denotes cathode
- ◇ Weight: 0.008 ounces, 0.23 grams
- ◇ Mounting position: Any

A - 405



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate by 20%.

		ER 100S	ER 101S	ER 101AS	ER 102S	ER 103S	ER 104S	ER 106S	UNITS
Maximum recurrent peak reverse voltage	V _{RRM}	50	100	150	200	300	400	600	V
Maximum RMS voltage	V _{RMS}	35	70	105	140	210	280	420	V
Maximum DC blocking voltage	V _{DC}	50	100	150	200	300	400	600	V
Maximum average forward rectified current 9.5mm lead length, @T _A =75°C	I _{F(AV)}	1.0							A
Peak forward surge current 8.3ms single half-sine-wave superimposed on rated load @T _J =125°C	I _{FSM}	30.0							A
Maximum instantaneous forward voltage @ 1.0A	V _F	0.95				1.25		1.7	V
Maximum reverse current @T _A =25°C at rated DC blocking voltage @T _A =100°C	I _R	5.0 150.0							μA
Maximum reverse recovery time (Note1)	t _{rr}	35							ns
Typical junction capacitance (Note2)	C _J	17							pF
Typical thermal resistance (Note3)	R _{θJA}	50							°C/W
Operating junction temperature range	T _J	- 55 ----- + 150							°C
Storage temperature range	T _{STG}	- 55 ----- + 150							°C


NOTE: 1. Measured with $I_F = 0.5\text{A}$, $I_R = 1\text{A}$, $t_{rr} = 0.25\text{A}$.

2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.


3. Thermal resistance junction to ambient

www.galaxycn.com

FIG.1 -- TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC



NOTES:1.RISE TIME = 7ns MAX.INPUT IMPEDANCE = 1MΩ .22pF.
2.RISE TIME =10ns MAX.SOURCE IMPEDANCE=50 Ω .



SET TIME BASE FOR 5 ns/cm

FIG.2 -- TYPICAL FORWARD CHARACTERISTIC




FIG.3 -- FORWARD DERATING CURVE




FIG.4 -- TYPICAL JUNCTION CAPACITANCE




FIG.5 -- PEAK FORWARD SURGE CURRENT

