



Part No. 1107741 and 1108800 Oscillator Sockets

FEATURES:

- This four pin socket (in 14 & 8 position frames) accept standard oscillator packages.
- Designed to be end-to-end or side-to-side stackable.
- Machine insertable.

SPECIFICATIONS:

- Body material is black UL 94V-0 Glass-filled 4/6 Nylon.
- Pin body is Brass Alloy 360 1/2 hard per UNS C36000 ASTM-B16-00.
- Pin body plating is 200μ [5.08 μ m] min Tin per ASTM B 545 Type 1 over 100μ [2.54 μ m] min. Nickel per SAE-AMS-QQ-N-290.
- 4-fingered collet contact is Beryllium Copper Alloy per UNS C17200 ASTM-B194-01.
- Contact plating is 10μ [.25 μ m] min. Gold per MIL-G-45204 over 50μ [1.27 μ m] min. Nickel per SAE-AMS-QQ-N-290.
- Contact current rating=3 Amps.
- Operating temperature=221°F [105°C].
- Insertion Force=180 grams/pin; Withdrawal Force=90 grams/pin; Normal Force=140 grams/pin; based on a .018 [.46] diameter test lead.
- Accepts leads .015-.025 [.38-.64] in diameter, .100-.146 [2.54-3.71] in length.

MOUNTING CONSIDERATIONS:

- Suggested PCB hole size=.030 ± .002 [.76 ± .05] dia.




Note: Aries specializes in custom design and production. In addition to the standard products shown on this page, special materials, platings, sizes, and configurations can be furnished, depending on quantities. Aries reserves the right to change product specifications without notice.

ORDERING INFORMATION



1107741 = 14 Pin (Tin Shell/Gold Collet)
 1107741-TL = 14 Pin (Tin/Lead Shell/Gold Collet)
 1108800 = 8 Pin (Tin Shell/Gold Collet)
 1108800-TL = 8 Pin (Tin/Lead Shell/Gold Collet)

CONTACT DETAIL



ALL DIMENSIONS: INCHES [MILLIMETERS]

All tolerances ± .005 [.13]
unless otherwise specified



<http://www.arieselec.com> • info@arieselec.com

Bristol, PA USA
TEL: (215) 781-9956
FAX: (215) 781-9845



14005
REV. F

PRINTOUTS OF THIS DOCUMENT MAY BE OUT OF DATE AND SHOULD BE CONSIDERED UNCONTROLLED