





TYP AT POST TIPS

$\varnothing 0.38[.015]M$



0.64 ± 0.03
[.025±.001] TYP

$\varnothing 0.38[.015]M$

TYP AT POST TIPS

1

1.68 ± 0.05
[.066±.002] 2 PLC

C REF

A SPACES AT $2.54[.100]$ = B

1.02
[.040]
3 PLC

$2.54[.100]$

ROW X

ROW Y

POSN. NO. REF

1 2 3

10.16±0.08
[.400±.003]

2.29 ± 0.05
[.090±.002]
2 PLC

1

8.13±0.25
[.320±.010]

5.08
[.200]
(CONTACT AREA)

0.64 ± 0.05
[.025±.002] TYP

$\varnothing 0.38[.015]M$

TYP AT POST TIPS

2

2.54
[.100]

6.35±0.38
[.250±.015]

$\varnothing 0.38[.015]M$

TYP AT POST TIPS

2.29 ± 0.05
[.090±.002]

SECTION X—X

2.54±0.08
[.100±.003]

$\varnothing 1.02\pm0.08$
[$\varnothing 0.040\pm0.003$]DIA TYP
(HOLE SIZE BEFORE PLATING,
1.148±0.03 [.0452±.0010]
DIA TYP)

RECOMMENDED HOLE LAYOUT

6	5,15,20,25	8,13	58.57 [2.306]	2.69 [.106]	64.31 [2.532]	60.96 [2.400]	24	50	5-147078-4
6	1,6,11,21	13,18	58.57 [2.306]	2.69 [.106]	64.31 [2.532]	60.96 [2.400]	24	50	5-147078-3
6	9	9,10	20.47 [.806]	2.69 [.106]	26.21 [1.032]	22.86 [.900]	9	20	5-147078-2
6	2,4,9	2,4,9	20.47 [.806]	2.69 [.106]	26.21 [1.032]	22.86 [.900]	9	20	5-147078-1
5	5,15,20,25	8,13	58.57 [2.306]	2.69 [.106]	64.31 [2.532]	60.96 [2.400]	24	50	147078-4
5	1,6,11,21	13,18	58.57 [2.306]	2.69 [.106]	64.31 [2.532]	60.96 [2.400]	24	50	147078-3
5	9	9,10	20.47 [.806]	2.69 [.106]	26.21 [1.032]	22.86 [.900]	9	20	147078-2
5	2,4,9	2,4,9	20.47 [.806]	2.69 [.106]	26.21 [1.032]	22.86 [.900]	9	20	147078-1
PLATING	ROW Y	ROW X	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

B. HAYMAKER

18AUG98

CHK

J. GESFORD

18AUG98

APVD

J. GESFORD

18AUG98

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± 0.13[.005]

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH SEE TABLE

tyco

Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

HDR ASSY, MOD II, ACTION
PIN, DBL ROW, .100X.100 C/L,
4 SIDED SHROUD, SELECT LOAD

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=147078

RESTRICTED TO

—

SCALE

3:1

SHEET

1

OF

1

REV

C

AMP 1471-9 REV 31MAR2000