







8			7		
THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION		
COPYRIGHT 20			20		
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.					
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION
1852829-1	A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER
1852829-2	A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER
1852829-3	A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER
1852829-6	A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER
7-1852829-7	A	-	-	-	SPARE PARTS

- △ RECOMMENDED SPARE PARTS
△ GREASE LIGHTLY
△ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE



TERMINAL NAME: SRC-A, CRIMP SNAP-IN					
TE PN	ERNIE	ERNIE TERMINAL - TE CRIMP SPECS			
1949935-1	37404				
-	-	PAD LTR	CRIMP HEIGHT	WIRE SIZE	
-	-	A	1.57mm+.05/- .05[.062+.002/- .002]	16AWG	
-	-	B	1.37mm+.05/- .05[.054+.002/- .002]	18AWG	
-	-	C			
-	-	D			
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	1.78mm [.070]	F	16-18 AWG
-	-	INSUL	2.03mm [.080]	O	Ø 1.473 MAX
WIRE STRIP LENGTH 1.88-2.26	TERM APPL SPEC NONE	FEED 7.70	APPLICATOR INSTRUCTIONS 408-8040		SET UP GAGE 458637-1



DIST		REVISIONS						
A	66	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		A		RELEASED	08JUN2009	RK	TE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852829-3](#)