

2.1x0.6mm RIGHT ANGLE SURFACE LED


XZUR74W



SUN LED

Email : sales@us.sunled.com

Web Site : www.sunled.com



Notes:


1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.1(0.004)$ unless otherwise noted.

Absolute maximum ratings ($T_A=25^{\circ}\text{C}$)		UR (GaAsP/GaP)	Unit
Reverse voltage	V_R	5	V
Forward current	I_F	30	mA
Forward current (peak) 1/10Duty cycle 0.1ms pulse width	i_{FS}	160	mA
Power dissipation	P_T	105	mW
Operating temperature	T_A	-40 ~ +85	$^{\circ}\text{C}$
Storage temperature	T_{stg}		





Operating Characteristics ($T_A=25^{\circ}\text{C}$)		UR (GaAsP/GaP)	Unit
Forward voltage (typ.) ($I_F=20\text{mA}$)	V_F	2.0	V
Forward voltage (max.) ($I_F=20\text{mA}$)	V_F	2.5	V
Reverse current ($V_R=5\text{V}$)	I_R	10	μA
Wavelength at peak emission ($I_F=20\text{mA}$)	λ_{peak}	627	nm
Wavelength at Dominate emission ($I_F=20\text{mA}$)	λ_D	625	nm
Spectral Line half-width ($I_F=20\text{mA}$)	$\Delta\lambda$	45	nm
Capacitance ($V_F=0\text{V}$, $f=1\text{MHz}$)	C	15	pF

Part Number	Emitting Color	Emitting Material	Lens-color	Luminous Intensity ($I_F=20\text{mA}$) mcd min. typ.		Wavelength nm λ_P	Viewing Angle $2\theta_{1/2}$
XZUR74W	Red	GaAsP/GaP	Water Clear	4	13	627	120°

XZUR74W




◆UR




XZUR74W

❖SMT Reflow Soldering Instructions



❖Recommended Soldering Pattern (Units : mm; Tolerance: ± 0.1)



❖Tape Specification (Units : mm)

