

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC

DIST

FT

0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	CI	REVISED PER ECO-12-007964	02MAY2012	KH	MS

10.0±0.1

2.50 REF

1.00±0.02

1

2

3

4

5

MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.

SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.

NOT CUMULATIVE TOLERANCE.

282827-2 AS SHOWN

A

8.35±0.15

12.0

1.00±0.02

3.9

3.85

3.5±0.3

RECOMMENDED PC BOARD LAYOUT

1.4

+0.1

-0

10.0

0.1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.3

1 PLC ±.3

2 PLC ±.25

3 PLC ±.25

4 PLC ±.25

ANGLES ±2

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

31JUL2001

31JUL2001

31JUL2001

108-20166

114-20079

-

TE Connectivity

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TERMINAL BLOCK HEADER ASSEMBLY

180 DEGREE OPEN ENDS

10mm PITCH

A300779

C-282827

-

CUSTOMER DRAWING

SCALE

3:1

SHEET

1

OF

1

REV

CI

1470-19 (3/11)

Pro/ENGINEER DRAWING