



Wiha. Premium Tools
for Professionals.

Wiha Square Handle. The Classic Screwdriver for Multiple Applications.

*Wiha Square handle,
impact resistant and
cadmium-free –
also withstands a few
hammer strokes.*



Square Handle Advantages:

- Robust, large-surface handle made of impact-resistant plastic material, chemical and oil-resistant
- Smooth handle surface allows easy cleaning
- Wiha ChromeTop-finish on tip for a perfect fit every time
- Takes up a small amount of space in the toolbox

The Wiha Square handle screwdriver is the classic screwdriver for everyday use in multiple applications.

Its robust handle is manufactured from high quality plastic and is impact-resistant, non-splintering and recyclable.

Users appreciate its multiplicity and high quality, which is also expressed through the hardened chrome-vanadium-molybdenum steel blade.





Wiha. Premium Tools
for Professionals.

Wiha Square Handle. The Classic Screwdriver for Multiple Applications.

For Phillips & Pozidriv Screws.



153 Phillips Screwdriver.

Blade: Round blade.
Chrome-vanadium steel, through hardened, nickel-plated.

Handle: Wiha Square handle, oil and grease resistant.

Standards: ISO 8764.

Application: Traditional square handle design for everyday use in multiple applications.

Order-No.	+			•	+	
00109 4	0	60	135	3.0	19	10
00111 7	1	80	175	4.5	24	10
00112 4	1•	200	295	4.5	24	10
00115 5	2	100	205	6.0	28	10
00116 2	2•	250	355	6.0	28	10
00117 9	2•	350	455	6.0	28	5
00119 3	3	150	265	8.0	32	10
00120 9	3•	300	415	8.0	32	5
00121 6	4	200	325	10.0	36	5

• Non-DIN sizes.



160 Phillips Screwdriver.


Blade: Round blade, hex bolster for additional torque.
Chrome-vanadium steel, through hardened, nickel-plated.

Handle: Wiha Square handle, oil and grease resistant.

Standards: ISO 8764.

Application: Traditional square handle design for everyday use in multiple applications.

Order-No.	+			•	+	
00138 4	1	80	175	4.5	8	24
00140 7	2	100	205	6.0	10	28
00142 1	3	150	265	8.0	13	32



222 Pozidriv Screwdriver.

Blade: Round blade.
Chrome-vanadium steel, through hardened, nickel-plated.

Handle: Wiha Square handle, oil and grease resistant.

Standards: ISO 8764.

Application: Traditional square handle design for everyday use in multiple applications.

Order-No.	+			•	+	
00416 3	0	60	135	3.0	75	19
00418 7	1	80	175	4.5	95	24
00419 4	1•	200	295	4.5	95	24
00422 4	2	100	205	6.0	105	28
00423 1	2•	250	355	6.0	105	28
00426 2	3	150	265	8.0	115	32

• Non-DIN sizes.

For TORX® Screws and Hex Nuts.



360 TORX® Screwdriver.

Blade: Chrome-vanadium steel, through hardened, black-finish.

Handle: Wiha Square handle, oil and grease resistant.

Application: Traditional square handle design for everyday use in multiple applications.

Order-No.				•	+	
26115 3	T3	50	110	2.5	14	10
26117 7	T4	50	110	2.5	14	10
05280 5	T5	50	110	2.5	14	10
01264 9	T6	50	125	3.5	19	10
01265 6	T7	50	125	3.5	19	10
01266 3	T8	60	135	3.5	19	10
01267 0	T9	60	145	4.0	22	10
01268 7	T10	80	175	4.0	24	10
01269 4	T15	80	175	4.0	24	10
01270 0	T20	100	205	4.0	28	10
01271 7	T25	100	205	4.5	28	10
01273 1	T30	115	230	6.0	32	5



342 Nut Driver.

Blade: Chrome-vanadium steel, through hardened, nickel-plated.
Deep drawn socket.

Handle: Wiha Square handle, oil and grease resistant.

Standards: DIN 3125.

Application: Traditional square handle design for everyday use in multiple applications.

Order-No.	+			•	+	
01051 5	3	125	220	24	10	
01053 9	3.5	125	220	24	10	
01054 6	4	125	220	24	10	
01055 3	4.5	125	220	24	10	
01056 0	5	125	220	24	10	
01057 7	5.5	125	220	24	10	
01058 4	6	125	220	24	10	
01059 1	7	125	230	28	10	
01060 7	8	125	230	28	10	
01061 4	9	125	230	28	10	
01062 1	10	125	230	28	10	
01063 8	11	125	240	32	10	
01064 5	12	125	240	32	10	
01065 2	13	125	240	32	10	