



0496




0496-0-15-XX-23-XX-10-0
Press-fit in 2,69 mounting hole

0368




0368-0-33-XX-13-XX-10-0
Wire Crimp Termination. Accepts wire sizes 16 AWG Max. / 20 AWG Min.

8067




8067-0-19-XX-13-XX-10-0
Wire Crimp Termination. Accepts wire sizes 24 AWG Max. / 28 AWG Min.

1105




1105-0-15-XX-13-XX-04-0
Press-fit in 2,03 mounting hole

8730




8730-0-19-XX-23-XX-10-0
Wire Crimp Termination. Accepts wire sizes 22 AWG Max. / 26 AWG Min.

3667




3667-0-19-XX-23-XX-10-0
Wire Crimp Termination. Accepts wire sizes 18 AWG Max. / 22 AWG Min.

9372




9372-0-15-XX-23-XX-10-0
Solder mount in 2,59 min. mounting hole

4582




4582-0-15-XX-23-XX-10-0
Square press-fit in 1,02 plated thru hole

5834




5834-0-15-XX-23-XX-10-0
Press-fit in 2,72 mounting hole

9401




9401-0-15-XX-23-XX-10-0
Solder mount in 2,59 min. mounting hole
Also available on 24mm wide carrier tape: 1,100 parts per 330mm reel.
Order as: 9401-0-57-XX-23-XX-10-0

9801



9801-0-15-XX-23-XX-10-0
Solder mount in 2,59 min. mounting hole
Also available on 16mm wide carrier tape: 1,200 parts per 330mm reel.
Order as: 9801-0-57-XX-23-XX-10-0

8829



8829-0-15-XX-23-XX-10-0
Solder mount in 2,59 min. mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm 0,13$
DIAMETERS: $\pm 0,05$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- 80 5,08 μ m TIN OVER NICKEL (RoHS)
- 15 0,25 μ m GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- 80 5,08 μ m TIN OVER NICKEL (RoHS)
- 27 0,76 μ m GOLD OVER NICKEL (RoHS)

SELECT CONTACT

#13 or #23 CONTACT (DATA ON PAGE 226)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[5834-0-15-01-23-01-10-0](#) [5834-0-15-01-23-27-10-0](#) [4582-0-15-01-23-01-10-0](#) [4582-0-15-01-23-27-10-0](#) [5834-0-15-80-23-80-10-0](#) [4582-0-15-80-23-80-10-0](#) [4582-0-15-80-23-27-10-0](#) [4582-0-15-15-23-27-10-0](#) [5834-0-15-15-23-27-10-0](#)