

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A

A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

V3-1113

CK-MI350

CATALOG

5

V3-1113

M

DRAWING
NUMBER

2

4

ISSUE

2

4

CHECK

REVISIONS

A

C039182

C E B

10 FEB 78

B

C074635

K O R

10 MAY 93

C

C077796

D C S

24 MAR 94

CHECK

121 MAR 74

CHECK

74

MAR

20



D B W

DRAWN

FO-52848

REPLACES X61345-V3

RELEASE NO. PR-4024



NOTE -

1 - TERMINALS ARE PLATED FOR SOLDERING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — 75 GRAMS MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE TRAVEL — — — .010 MIN		UNLESS OTHERWISE NOTED
RELEASE FORCE — — — 10 GRAMS MIN		DIMENSIONS ARE IN INCHES
		TOLERANCES ARE
DIFFERENTIAL TRAVEL — — — .002-.010	L112 10A 1/3HP 125 OR 250 VAC	ONE PLACE (.01) ± .030
OVERTRAVEL — — — .050 MIN	1/2A 125 VDC, 1/4A 250 VDC	TWO PLACE (.00) ± .015
FREE POSITION — — — .625 MAX	4A 125 VAC "L"	THREE PLACE (.000) ± .005
		ANGLES ±
		WEIGHT

