















(D)			
12	POST-TIN (POST-ETAME)	BRASS (LAITON)	TAB 1.5 X 0.8 (LANGUETTE 1.5 X 0.8)
4	POST-TIN (POST-ETAME)	BRASS (LAITON)	TAB 2.8 X 0.8 (LANGUETTE 2.8 X 0.8)
1	-	PBT 20GF	16 W HOUSING (BOITIER 16 V)
QTY (QTE)	FINITION	MATERIAL (MATIERE)	DESIGNATION

CODINGS (DETROMPAGES)						
P/N TE (REF. TE)	953371-1	BLACK (NOIR)	 ECHELLE 1:1	953371-4	WHITE (BLANC)	 ECHELLE 1:1
	953371-2	GREEN (VERT)	 ECHELLE 1:1	953371-5	BROWN (MARRON)	 ECHELLE 1:1
	953371-3	BLUE (BLEU)	 ECHELLE 1:1	953371-6	GREY (GRIS)	 ECHELLE 1:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG/DESIGN 03MAR98		 TE Connectivity	
CE PLAN EN DOCUMENT CONTRÔLÉ PAR L'INVENTAIRE EST DOSSIERÉ ET ÉTÉRIE VOIR: CONTRÔLE ET SERVICE TECHNIQUE - 5000 - 10000 - 10000 - 10000 - 10000		CNR/VERIFIER J. LAUREN			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED		NAME	
mm		TOLERANCES NOT SPECIFIED (AS PER DECIMALS):		TITLE	
		PRODUCT SPEC SPEC. PRODUCT		16V MCP HYB RIGHT ANGLE HEADER EMASE COUDEE 16V HYBRIDE MCP	
ANGLES 45		APPLICATION SPEC SPEC. APPLICATION		SIZE FORMAT	
MATERIAL MATIERE		WEIGHT MASSE APPROX.		DRAWING NO NO PLAN	
FINISH FINITION		CUSTOMER DRAWING /PLAN CLIENT		A100779 C=953371	
		EQUIPMENT POUR REFERENCE		RESTRICTED TO RESERVE A	
		SCALE ECHALE		SHEET FEUILLE	
		OF DE		REV F	