






DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION

- NOTES:
- 1 SEE SHEET 2 FOR 216564-2, 6 POS./4 CONTACTS.
 - 2 TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,15$
 - 3 FOR APPLICATION INFORMATION SEE AMP SPEC. 114-19019.
 - 4 FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108-19064



PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]

TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,05$.


PRINTED CIRCUIT BOARD THICKNESS: 1,6 mm NOMINAL.

700pcs. ON A 60cm. DIA. REEL	6 POSITIONS/ 6 CONTACTS.	IN CONTACT AREA: 1,2µm MIN. SEL. GOLD OVER 1,2µm MIN. NICKEL SOLDER TINES: 2,0µm MIN. TIN-LEAD OVER 1,2µm MIN. NICKEL	HOUSING: PTB,UL 94-HB COLOR: BLACK CONTACTS: PHOSPHOR BRONZE	216564-1
REMARKS	REMARKS	FINISH	MATERIAL	PARTNUMBER
-	-	-	-	-
-	-	-	-	-
H2	ECR-08-013498	AEG	-	18-02-09
H1	OU60-0073-00	KV	KV	10 AUG 00
H	EH-1376-99	MVE	MVE	22 JUL 99
G	EH-0939-99	JG	TD	APR 99
F	EH-0244-96	MVE	G.C.	15 FEB 96
LTR.	REVISION RECORD	DR.	CHK.	DATE
DR.: L.v.d.HETDEN	CHK.: C.STERKEN	APP.: L.v.SOEST	DWG.No.	REV.LTR.
DATE: 29 AUG 89	DATE: -	DATE: -	C- 216564	H2
				SHEET 1 OF 2
				A2






DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



- NOTES:
- 1 SEE SHEET 1 FOR 216564-1, 6 POS/6 CONTACTS.
 - 2 TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,15$
 - 3 FOR APPLICATION INFORMATION SEE AMP SPEC. 114-19019.
 - 4 FOR PERFORMANCE REQUIREMENTS SEE AMP SPEC. 108-19064



PRINTED CIRCUIT BOARD LAYOUT

[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]

TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0,05$.

PRINTED CIRCUIT BOARD THICKNESS: 1,6 mm NOMINAL.

OBSOLETE

BULK PACKAGED 1000pcs. IN A BOX		6 POSITIONS/ 4 CONTACTS.		IN CONTACT AREA: 1,2µm MIN. SFL. GOLD OVER 1,2µm MIN. NICKEL		HOUSING: RTB, UL 94 HB COLOR: BLACK		216564-5	
700pcs. ON A 60cm DIA. REEL				SOLDER TINES: 2,0µm MIN. TIN-LEAD OVER 1,2µm MIN. NICKEL		CONTACTS: PHOSPHOR BRONZE		216564-2	
PACKAGING		REMARKS		FINISH		MATERIAL		PARTNUMBER	
-	-	-	-	-	-	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED (C) COPYRIGHT 19 BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING. THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION, 19 AMP AMP HOLLAND B.V. 's-Hertogenbosch, The Netherlands. NAME MODULAR JACK, 6 POS./4 CONT., TOP ENTRY, WITH PANEL STOPS, FOR PRINTED CIRCUIT BOARD.			
-	-	-	-	-	-				
-	-	-	-	-	-				
-	-	-	-	-	-				
-	-	-	-	-	-				
-	SEE SHEET 1	-	-	-	-				
-	-	-	-	-	-				
LTR.		DR.	CHK.	DATE					
DR.:	P.BEIJNON	CHK.:	C.STERKEN	APP.:	L.v.SOEST	DWG.No.		REV.LTR.	SHEET
DATE:	-	DATE:	-	DATE:	-	C- 216564		H2	2 OF 2
								A2	