

TOSHIBA BIPOLAR LINEAR INTEGRATED CIRCUIT SILICON MONOLITHIC


TA79005SB, TA79006SB, TA79007SB, TA79008SB, TA79009SB, TA79010SB
TA79012SB, TA79015SB, TA79018SB, TA79020SB, TA79024SB

1 A THREE TERMINAL NEGATIVE VOLTAGE REGULATORS

-5 V, -6 V, -7 V, -8 V, -9 V, -10 V, -12 V, -15 V, -18 V,
-20 V, -24 V


FEATURES

- Suitable for CMOS, TTL, and the other Digital IC Power Supply
- Internal Thermal Overload Protecting
- Internal Short Circuit Current Limiting
- Output Current in Excess of 1.0 A
- Package in the plastic case TPL ($P_D = 1.8 W$)



Weight : 1.5 g (Typ.)

EQUIVALENT CIRCUIT



000707EBA2

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc.
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.

MAXIMUM RATINGS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	RATING	UNIT
Input Voltage	TA79005SB	V _{IN}	- 35	V
	TA79006SB			
	TA79007SB			
	TA79008SB			
	TA79009SB			
	TA79010SB			
	TA79012SB			
	TA79015SB			
	TA79018SB			
	TA79020SB			
TA79024SB	- 40			
Power Dissipation	(Ta = 25°C)	P _D	1.8	W
Operating Temperature		T _{opr}	- 30~85	°C
Storage Temperature		T _{stg}	- 55~150	°C
Junction Temperature		T _j	150	°C
Thermal Resistance		R _{th(j-a)}	69.4	°C / W

000707EBA2'

- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

TA79005SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -10\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-5.2	-5.0	-4.8	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	—	7	50	mV
			$-12\text{ V} \leq V_{IN} \leq -8\text{ V}$ $-25\text{ V} \leq V_{IN} \leq -7\text{ V}$	—	35	100	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	—	11	100	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	—	4	50	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-20\text{ V} \leq V_{IN} \leq -7\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-5.25	—	-4.75	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	—	4.3	8.0	mA
Quiescent Current Change	Line	1	$-25\text{ V} \leq V_{IN} \leq -7\text{ V}$, $T_j = 25^\circ\text{C}$	—	—	1.3	mA
	Load	1	$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	—	—	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	—	40	—	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	63	70	—	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	—	1.9	—	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	—	0.6	—	$\text{mV}/^\circ\text{C}$

TA79006SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -11\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIR- CUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-6.25	-6.0	-5.75	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	—	9	60	mV
			$-13\text{ V} \leq V_{IN} \leq -9\text{ V}$ $-25\text{ V} \leq V_{IN} \leq -8\text{ V}$	—	43	120	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	—	13	120	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	—	5	60	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-21\text{ V} \leq V_{IN} \leq -8\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-6.3	—	-5.7	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	—	4.3	8.0	mA
Quiescent Current Change	Line	1	$-25\text{ V} \leq V_{IN} \leq -8\text{ V}$, $T_j = 25^\circ\text{C}$	—	—	1.3	mA
	Load	1	$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	—	—	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	—	45	—	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	61	68	—	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	—	1.9	—	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	—	0.7	—	$\text{mV}/^\circ\text{C}$

TA79007SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -12\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-7.28	-7.0	-6.72	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	—	10	70	mV
			$-15\text{ V} \leq V_{IN} \leq -10\text{ V}$ $-25\text{ V} \leq V_{IN} \leq -9\text{ V}$	—	45	140	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	—	20	140	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	—	7	70	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-22\text{ V} \leq V_{IN} \leq -9\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-7.35	—	-6.65	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	—	4.3	8.0	mA
Quiescent Current Change	Line	1	$-25\text{ V} \leq V_{IN} \leq -9\text{ V}$, $T_j = 25^\circ\text{C}$	—	—	1.0	mA
	Load		$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	—	—	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	—	49	—	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	60	67	—	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	—	1.9	—	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	—	0.9	—	$\text{mV}/^\circ\text{C}$

TA79008SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -14\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-8.3	-8.0	-7.7	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	-	11	80	mV
			$-17\text{ V} \leq V_{IN} \leq -11\text{ V}$ $-25\text{ V} \leq V_{IN} \leq -10.5\text{ V}$	-	47	160	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	-	26	160	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	-	9	80	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-23\text{ V} \leq V_{IN} \leq -10.5\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-8.4	-	-7.6	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	-	4.3	8.0	mA
Quiescent Current Change	Line	1	$-25\text{ V} \leq V_{IN} \leq -10.5\text{ V}$, $T_j = 25^\circ\text{C}$	-	-	1.0	mA
	Load	1	$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	-	-	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	-	52	-	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	59	66	-	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	-	1.9	-	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	-	2.0	-	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	-	1.0	-	$\text{mV}/^\circ\text{C}$

TA79009SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -15\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-9.3	-9.0	-8.7	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	—	11	82	mV
			$-19\text{ V} \leq V_{IN} \leq -13\text{ V}$ $-26\text{ V} \leq V_{IN} \leq -11.5\text{ V}$	—	48	162	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	—	33	162	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	—	11	82	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-24\text{ V} \leq V_{IN} \leq -11.5\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-9.4	—	-8.6	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	—	4.3	8.0	mA
Quiescent Current Change	Line	1	$-26.5\text{ V} \leq V_{IN} \leq -13\text{ V}$, $T_j = 25^\circ\text{C}$	—	—	1.0	mA
	Load		$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	—	—	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	—	60	—	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	57	64	—	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	—	1.9	—	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	—	1.1	—	$\text{mV}/^\circ\text{C}$

TA79010SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -16\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-10.4	-10	-9.6	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	-	12	90	mV
			$-20\text{ V} \leq V_{IN} \leq -14\text{ V}$ $-27\text{ V} \leq V_{IN} \leq -12.5\text{ V}$	-	50	180	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	-	40	180	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	-	13	90	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-25\text{ V} \leq V_{IN} \leq -12.5\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-10.5	-	-9.5	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	-	4.4	8.0	mA
Quiescent Current Change	Line	1	$-27.5\text{ V} \leq V_{IN} \leq -14\text{ V}$, $T_j = 25^\circ\text{C}$	-	-	1.0	mA
	Load	1	$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	-	-	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	-	65	-	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	57	63	-	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	-	1.9	-	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	-	2.0	-	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	-	1.3	-	$\text{mV}/^\circ\text{C}$

TA79012SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -19\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	1	T _j = 25°C		− 12.5	− 12	− 11.5	V
Line Regulation	Reg·line	1	T _j = 25°C	− 22 V ≤ V _{IN} ≤ − 16 V	—	13	120	mV
				− 30 V ≤ V _{IN} ≤ − 14.5 V	—	55	240	
Load Regulation	Reg·load	1	T _j = 25°C	5 mA ≤ I _{OUT} ≤ 1.5 A	—	46	240	mV
				250 mA ≤ I _{OUT} ≤ 750 mA	—	17	120	
Output Voltage	V _{OUT}	1	T _j = 25°C	− 27 V ≤ V _{IN} ≤ − 14.5 V 5 mA ≤ I _{OUT} ≤ 1.0 A	− 12.6	—	− 11.4	V
Quiescent Current		I _B	1	T _j = 25°C	—	4.4	8.0	mA
Quiescent Current Change	Line	ΔI _B	1	− 30 V ≤ V _{IN} ≤ − 14.5 V, T _j = 25°C	—	—	1.0	mA
	Load		1	5 mA ≤ I _{OUT} ≤ 1.0 A, T _j = 25°C	—	—	0.5	
Output Noise Voltage		V _{NO}	2	T _a = 25°C, I _{OUT} = 20 mA, 10 Hz ≤ f ≤ 100 kHz	—	75	—	μV _{rms}
Ripple Rejection		R.R.	3	f = 120 Hz, I _{OUT} = 20 mA, T _j = 25°C	54	61	—	dB
Short Circuit Current Limit		I _{SC}	1	T _j = 25°C	—	1.9	—	A
Dropout Voltage		V _D	1	T _j = 25°C, I _{OUT} = 1.0 A	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage		T _{CVO}	1	I _{OUT} = 5.0 mA	—	1.6	—	mV / °C

TA79015SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -23\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-15.6	-15	-14.4	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	—	14	150	mV
			$-26\text{ V} \leq V_{IN} \leq -20\text{ V}$ $-30\text{ V} \leq V_{IN} \leq -17.5\text{ V}$	—	57	300	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	—	68	300	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	—	25	150	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-30\text{ V} \leq V_{IN} \leq -17.5\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-15.75	—	-14.25	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	—	4.4	8.0	mA
Quiescent Current Change	Line	1	$-30\text{ V} \leq V_{IN} \leq -17.5\text{ V}$, $T_j = 25^\circ\text{C}$	—	—	1.0	mA
	Load	1	$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	—	—	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	—	90	—	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	53	60	—	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	—	1.9	—	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	—	2.0	—	$\text{mV}/^\circ\text{C}$

TA79018SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -27\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-18.7	-18	-17.3	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	—	25	180	mV
			$-30\text{ V} \leq V_{IN} \leq -24\text{ V}$ $-33\text{ V} \leq V_{IN} \leq -21\text{ V}$	—	80	360	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	—	110	360	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	—	55	180	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-33\text{ V} \leq V_{IN} \leq -21\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-18.85	—	-17.15	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	—	4.5	8.0	mA
Quiescent Current Change	Line	ΔI_B	1	—	—	1.0	mA
	Load		1	—	—	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	—	110	—	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	52	59	—	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	—	1.9	—	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	—	2.5	—	$\text{mV}/^\circ\text{C}$

TA79020SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -30\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)

CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
Output Voltage	V _{OUT}	1	T _j = 25°C		- 20.8	- 20	- 19.2	V
Line Regulation	Reg·line	1	T _j = 25°C	- 32 V ≤ V _{IN} ≤ - 26 V	—	28	180	mV
				- 35 V ≤ V _{IN} ≤ - 24 V	—	104	360	
Load Regulation	Reg·load	1	T _j = 25°C	5 mA ≤ I _{OUT} ≤ 1.5 A	—	130	360	mV
				250 mA ≤ I _{OUT} ≤ 750 mA	—	70	180	
Output Voltage	V _{OUT}	1	T _j = 25°C	- 35 V ≤ V _{IN} ≤ - 24 V 5 mA ≤ I _{OUT} ≤ 1.0 A	- 21.0	—	- 19.0	V
Quiescent Current		I _B	1	T _j = 25°C	—	4.6	8.0	mA
Quiescent Current Change	Line	ΔI _B	1	- 36.5 V ≤ V _{IN} ≤ - 25 V, T _j = 25°C	—	—	1.0	mA
	Load		1	5 mA ≤ I _{OUT} ≤ 1.0 A, T _j = 25°C	—	—	0.5	
Output Noise Voltage	V _{NO}	2	T _a = 25°C, I _{OUT} = 20 mA, 10 Hz ≤ f ≤ 100 kHz		—	140	—	μV _{rms}
Ripple Rejection	R.R.	3	f = 120 Hz, I _{OUT} = 20 mA, T _j = 25°C		50	57	—	dB
Short Circuit Current Limit	I _{SC}	1	T _j = 25°C		—	1.9	—	A
Dropout Voltage	V _D	1	T _j = 25°C, I _{OUT} = 1.0 A		—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T _{CVO}	1	I _{OUT} = 5.0 mA		—	3.0	—	mV / °C


TA79024SB

ELECTRICAL CHARACTERISTICS (Unless otherwise specified, $V_{IN} = -33\text{ V}$, $I_{OUT} = 500\text{ mA}$,
 $0^\circ\text{C} \leq T_j \leq 125^\circ\text{C}$, $C_{IN} = 0.33\text{ }\mu\text{F}$, $C_{OUT} = 0.1\text{ }\mu\text{F}$)


CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$	-25.0	-24	-23.0	V
Line Regulation	Reg·line	1	$T_j = 25^\circ\text{C}$	—	31	240	mV
			$-36\text{ V} \leq V_{IN} \leq -30\text{ V}$ $-38\text{ V} \leq V_{IN} \leq -27\text{ V}$	—	118	480	
Load Regulation	Reg·load	1	$T_j = 25^\circ\text{C}$	—	150	480	mV
			$5\text{ mA} \leq I_{OUT} \leq 1.5\text{ A}$ $250\text{ mA} \leq I_{OUT} \leq 750\text{ mA}$	—	85	240	
Output Voltage	V_{OUT}	1	$T_j = 25^\circ\text{C}$ $-38\text{ V} \leq V_{IN} \leq -27\text{ V}$ $5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$	-25.2	—	-22.8	V
Quiescent Current	I_B	1	$T_j = 25^\circ\text{C}$	—	4.6	8.0	mA
Quiescent Current Change	Line	1	$-38\text{ V} \leq V_{IN} \leq -27\text{ V}$, $T_j = 25^\circ\text{C}$	—	—	1.0	mA
	Load		$5\text{ mA} \leq I_{OUT} \leq 1.0\text{ A}$, $T_j = 25^\circ\text{C}$	—	—	0.5	
Output Noise Voltage	V_{NO}	2	$T_a = 25^\circ\text{C}$, $I_{OUT} = 20\text{ mA}$, $10\text{ Hz} \leq f \leq 100\text{ kHz}$	—	170	—	μV_{rms}
Ripple Rejection	R.R.	3	$f = 120\text{ Hz}$, $I_{OUT} = 20\text{ mA}$, $T_j = 25^\circ\text{C}$	49	56	—	dB
Short Circuit Current Limit	I_{SC}	1	$T_j = 25^\circ\text{C}$	—	1.9	—	A
Dropout Voltage	V_D	1	$T_j = 25^\circ\text{C}$, $I_{OUT} = 1.0\text{ A}$	—	2.0	—	V
Average Temperature Coefficient Of Output Voltage	T_{CVO}	1	$I_{OUT} = 5.0\text{ mA}$	—	3.5	—	$\text{mV}/^\circ\text{C}$

TEST CIRCUIT


1. V_{OUT} , Reg.line, Reg.load, I_B , ΔI_B , V_D , T_{CVO}













2. V_{NO}



3. R.R.








PACKAGE DIMENSIONS
P-SIP3-2.50A

Unit : mm



Weight : 1.5 g (Typ.)