

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1052620003](#)
Status: **Active**
Overview: [Industrial, Scientific and Medical \(ISM\) Antennas](#)
Description: ISM 868/915MHz Antenna, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

Documents:	
3D Model	Application Specification AS-105262-0001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-105262-001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-105262-001-001 (PDF)	RoHS Certificate of Compliance (PDF)



General	
Product Family	Antennas
Series	105262
Component Type	Flexible Antenna with Cable
Function	Signal
Mates With	734120110 Microcoaxial RF, 50 Ohm
Overview	Industrial, Scientific and Medical (ISM) Antennas
Product Name	ISM 868/915 MHz Stand Alone
Protocol	LoRa, Neul, SigFox, Z-Wave, Zigbee
Type	ISM Antenna, LPWAN
UPC	887191106564

Physical	
Cable Length	200.00mm
Length	79.00mm
Mounting Style	Adhesive
Net Weight	0.929/g
Packaging Type	Tray
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	10.00mm

Electrical	
Band#1 F_End (MHz)	870
Band#1 F_Start (MHz)	863
Band#2 F_End (MHz)	928
Band#2 F_Start (MHz)	902
Electrical Connectivity	Cable
Peak Gain (dBi)	0.2 @ 868 MHz, 1.2 @ 915 MHz
Return Loss - S11 (dB)	< -11, < -13
Total Efficiency	> -2.0dB @ 915 MHz, > -3.2dB @ 868 MHz

Material Info	
Reference - Drawing Numbers	
Application Specification	AS-105262-0001-001
Packaging Specification	PK-105262-001-001
Product Specification	PS-105262-001-001
Sales Drawing	SD-105262-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[105262](#) Series