



Dimensions: in.

SPECIFICATIONS

Material:	UL approved Nylon 66, 94V-2
Packaged:	Parts are packaged 100 pieces per bag. Purchase in packaged quantities only.
Assembly:	Not Assembled

561-SL0809	
Description:	Snap Latch
G Min.:	0.084
G Max.:	0.173
H:	0.06
L:	0.38
W Dia.:	0.335
A:	0.28
B:	0.1
Hole Dia.:	.254-.250 (Fixed Structure)
T Max.:	0.065

561-SL0810	
Description:	Snap Latch
G Min.:	0.084
G Max.:	0.173
H:	0.06
L:	0.38
W Dia.:	0.335
A:	0.32
B:	0.27
Hole Dia.:	.254-.250 (Fixed Structure)
T Max.:	0.065

561-SL1010	
Description:	Snap Latch
G Min.:	0.118
G Max.:	0.207
H:	0.062
L:	0.44
W Dia.:	0.425
A:	0.36
B:	0.25
Hole Dia.:	.323-.316 (Fixed Structure)
T Max.:	0.098

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[561-SL0809](#) [561-SL0810](#) [561-SL1010](#)