



LOC		DIST		REVISIONS			
DY		F	LTR	DESCRIPTION		DATE	OWN
							APVD
		0		NPR FP00-0340-04		5JAN05	LWY
							LSF







MATING FACE




DETAIL D

- 1 SHIELD & CONTACTS: COPPER ALLOY.
HOUSING: POLYESTER, UL 94V-0 RATED, BLACK.
- 2 0.76 μm [.000030] MIN GOLD FOR A LENGTH OF 1.27 [.050] MIN FROM MATING END, 3.05 μm [.000120] MIN MATTE-TIN ON OPPOSITE END, BOTH OVER 1.27 μm [.000050] MIN NICKEL.
- 3 1.50-4.00 μm [.000059-.000158] THICK BRIGHT TIN.
- 4 GOLD PLATING PER MIL-G-45204, TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 5 DATUMS AND BASIC DIMENSION SUPPLIED BY CUSTOMER.



DETAIL F
SCALE 50:1



RECOMMENDED PC BOARD LAYOUT
BOTTOM VIEW

P/N: 5750069-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ANY DISCREPANCY BETWEEN THIS DRAWING AND THE CONTROLLING DOCUMENT ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		OWN WYLEE	05JAN2005	tyco Electronics Tyco Electronics Singapore Pte. Ltd.	
DIMENSIONS: mm [INCHES]		CHK SF LEONG	APVD SF LEONG		
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME	
0 PLC ± .013 [.005]		APPLICATION SPEC		RECEPTACLE ASSY, FRONT PANEL GROUNDING, 4 POS, RIGHT ANGLE, MINIATURE CIRCULAR DIN	
1 PLC ± .013 [.005]		WEIGHT		SIZE	
2 PLC ± .013 [.005]		CAGE CODE		CAGE CODE	
3 PLC ± .013 [.005]		FINISH		DRAWING NO	
4 PLC ± .013 [.005]		CUSTOMER DRAWING		A1 00779	
5 PLC ± .013 [.005]		SCALE		5:1	
6 PLC ± .013 [.005]		SHEET		1 OF 1	
7 PLC ± .013 [.005]		REV		0	