



Introducing Raychem Versaflex Expandable, Braided, Polyester Sleeving

Raychem brand Versaflex sleeving is suited for the mechanical protection of wire harnesses and hoses, and all other applications where the highest level of flexibility and abrasion/cut-through resistance is required. Versaflex sleeving serves as an economical means for wire bundling that will not trap heat or moisture, expanding easily to fit over irregular shapes, then contracting to conform to substrates. Versaflex sleeving comes in a flame-retardant (FR) version which meets the UL VW-1 flammability requirement. Versaflex sleeving must be cut with a hot knife to prevent fraying. This product is a cold applied expandable sleeving (non-heat shrink).



Raychem Versaflex Expandable, Braided, Polyester Sleeving

KEY FEATURES

- Expands and contracts easily to fit over a variety of substrates
- Lightweight and flexible
- Flame-retardant (FR) version available
- RoHS Compliant
- This product is cold applied

TE Technical Support Center

USA: +1 (800) 522-6752
Canada: +1 (905) 475-6222
Mexico: +52 (0) 55-1106-0800
Latin/S. America: +54 (0) 11-4733-2200
Germany: +49 (0) 6251-133-1999
UK: +44 (0) 800-267666
France: +33 (0) 1-3420-8686
Netherlands: +31 (0) 73-6246-999
China: +86 (0) 400-820-6015

te.com

© 2011 Tyco Electronics Corporation,
a TE Connectivity Ltd. Company. All Rights Reserved.
7-1773455-2 CIS PDF 03/2011

Raychem, Versaflex, TE Connectivity and TE connectivity
(logo) are trademarks. Other logos, product and/or company
names might be trademarks of their respective owners.

INDUSTRIES

- Commercial
- Industrial
- Rail
- Maintenance and Repair Organizations (MRO)
- Aerospace and Defense
- Marine

TEMPERATURE RATING

- Operating Temperature Range : -50°C to 150°C

STANDARDS AND SPECIFICATIONS

- UL E306976 VW-1, 125°C

ORDERING INFORMATION

Color	Versaflex: Black (-0) Versaflex FR: Black with white X tracer (-09)
Standard Packaging	On spools
Ordering Description	Specify product name, size and color (Example: VERSAFLEX FR-1/4-09-SP)

PRODUCT DIMENSIONS

Versaflex		Versaflex FR (Flame-Retardant)	
Size (in.)	Size Range mm [in]	Size (in.)	Size Range mm [in]
1/8	2.4-6.4 [0.094-0.252]	1/8	2.4-6.4 [0.094-0.252]
1/4	3.2-9.5 [0.125-0.375]	1/4	3.2-9.5 [0.125-0.375]
3/8	4.7-16 [0.185-0.630]	3/8	4.7-16 [0.185-0.630]
1/2	6.4-19 [0.252-0.748]	1/2	6.4-19 [0.252-0.748]
3/4	13-32 [0.512-1.260]	3/4	13-32 [0.512-1.260]
1-1/4	19-45 [0.748-1.772]	1-1/4	19-45 [0.748-1.772]
1-3/4	32-70 [1.260-2.756]	1-3/4	32-70 [1.260-2.756]
2	38-76 [1.496-2.992]	2	38-76 [1.496-2.992]



While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[VERSAFLEX-FR-1/2-09-SP](#) [VERSAFLEX-FR-1-1/4-09-SP](#) [VERSAFLEX-FR-3/4-09-SP](#) [VERSAFLEX-FR-3/8-09-SP](#)
[VERSAFLEX-1/2-0-SP](#) [VERSAFLEX-1/4-0-SP](#) [VERSAFLEX-1-1/4-0-SP](#) [VERSAFLEX-3/4-0-SP](#) [VERSAFLEX-3/8-0-SP](#)
[VERSAFLEX-FR-1/4-09-SP](#) [VERSAFLEX-FR-1/8-09-SP](#)