


ADSL LINE TRANSFORMERS

For GlobeSpan ADSL CPE Chipsets



- Matched to GlobeSpan's ATLAS and SLADE chipsets
- Excellent THD performance in a small footprint
- Designed to meet UL1950 and EN60950 supplementary insulation requirements for working voltages up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Chipset	Annex	Turns Ratio Chip - Line (±2%)	Inductance - Line Side @ 10 kHz, 100 mV (10-6) with (9-7) shorted	Leakage Inductance - Line Side @ 300 kHz, 0.1 Vrms (10-6) with (1,2,4,5) and (9-7) shorted	DC Resistance	
						Chip Side (1-5) with (2-4) shorted	Line Side (10-6) with (7-9) shorted
BX2260	Slade	A & C	1CS:2CS	440 µH ±5%	10 µH MAX	≤ 0.80 Ω	≤ 1.25 Ω
B2429	Atlas	A & C	1CS:1.6CS	440 µH ±5%	10 µH MAX	≤ 0.90 Ω	≤ 1.15 Ω
B2436	Atlas	B	1CS:1.6CS	100 µH ±5%	10 µH MAX	≤ 0.60 Ω	≤ 0.90 Ω

Additional Electrical Specifications



Part Number	Longitudinal Balance (from 20 kHz to 1 MHz)	THD at 100 Ω (@ 100 kHz, 4.242 Vrms)	Insertion Loss at 100 Ω (from 150 kHz to 1.1 MHz)	Interwinding Capacitance (@ 300 kHz, 0.1 Vrms)	Isolation Voltage (1 sec)
BX2260	≤ -50 dB	≤ -85 dB	≤ 0.60 dB	≤ 50 pF	1,875 Vrms
B2429	≤ -50 dB	≤ -85 dB	≤ 0.60 dB	≤ 50 pF	1,875 Vrms
B2436	≤ -50 dB	≤ -85 dB	≤ 0.60 dB	≤ 50 pF	1,875 Vrms

NOTE: Transformers are shipped in trays unless Tape & Reel packaging is specified by adding the suffix "T" to the part number (i.e. BX2260T).

Mechanical

Schematic

BX2260/B2429/B2436



Weight 6.2 grams
Tape & Reel 150/reel
Tray 60/tray

Dimensions: $\frac{\text{Inches}}{\text{mm}}$
Unless otherwise specified, all tolerances are $\pm \frac{.010}{0.25}$

For More Information :

UNITED STATES (Worldwide)	UNITED KINGDOM (Northern Europe)	FRANCE (Southern Europe)	SINGAPORE (Southern Asia)	TAIWAN, R.O.C. (Northern Asia)	HONG KONG (China/Hong Kong)	DISTRIBUTOR
12220 World Trade Drive San Diego, CA 92128 U.S.A. http://www.pulseeng.com TEL: 858 674 8100 FAX: 858 674 8262	1 & 2 Huxley Road The Surrey Research Park Guildford, Surrey GU2 5RE United Kingdom TEL: 44 1483 401700 FAX: 44 1483 401701	Zone Industrielle F-39270 Orgelet France TEL: 33 3 84 35 04 04 FAX: 33 3 84 25 46 41	150 Kampong Ampat #07-01/02 KA Centre Singapore 368324 TEL: 65 287 8998 FAX: 65 280 0080	3F-4, No. 81, Sec. 1 HsinTai Wu Road Hsi-Chih, Taipei Hsien Taiwan, R.O.C. Tel: 886 2 2698 0228 FAX: 886 2 2698 0948	19/F, China United Plaza 1008 Tai Nan West Street Cheung Sha Wan, Kowloon Hong Kong, China TEL: 852 2788 6588 FAX: 852 2776 1055	

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.