





Matchcode	Description	Picture	Technical data	Colours
<b>2 mm-Programme</b>				
EPB 6053 Ni / ..(colour)	<b>Press-in socket</b> <ul style="list-style-type: none"> <li>for pressing into panels up to 6 mm thick</li> <li>hole Ø 3.9</li> <li>accessoires: mounting with press-in tool WKZ EPB2</li> </ul>		terminal: PIN Ø 1.5 x 8 transition resistance: 7 mΩ rated voltage: 33 VAC / 70 VDC rated current: 10 A operating temperature: -40 °C ... +90 °C	black, red, blue, yellow, green, grey, brown, white, purple
KURZ 5741 / 5.08-2 IG MB Ni / ..(colour) KURZ 5741 / 5.08-2 IG MB Au / ..(colour)	<b>Connecting plug</b> <ul style="list-style-type: none"> <li>moulded insulation</li> <li>with rear socket Ø 2 mm</li> </ul>		terminal: socket transition resistance: 5 mΩ (Ni) / 3 mΩ (Au) rated voltage: 33 VAC / 70 VDC rated current: 12 A operating temperature: -40 °C ... +90 °C	black
<b>2 mm-Safety-Programme</b>				
SAK 6715 Ni / 2 / ..(colour)	<b>Safety crocodile clip</b> <ul style="list-style-type: none"> <li>insulated</li> <li>socket Ø 2 mm</li> <li>contact: crocodile jaws</li> <li>grips up to Ø 8 mm</li> </ul>		terminal: socket transition resistance: < 15 mΩ rated voltage: 600 V CAT II rated current: 10 A operating temperature: -25 °C ... +80 °C	black, red, blue, yellow, green, white
<b>4 mm-Programme</b>				
EPB 6792 Ni / ..(colour)	<b>Press-in socket</b> <ul style="list-style-type: none"> <li>for pressing into panels up to 6 mm thick</li> <li>hole Ø 6.8</li> <li>accessoires: mounting with press-in tool WKZ EPB4</li> </ul>		terminal: FR 4.8 x 0.8 transition resistance: 4 mΩ rated voltage: 33 VAC / 70 VDC rated current: 24 A operating temperature: -40 °C ... +90 °C	black, red, blue, yellow, green, grey, brown, white, purple