FAIRCHILD™

Is Now Part of

ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at
www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

FAN7601
## Green Current Mode PWM Controller

Features

- Green Current Mode PWM Control
- Low Operating Current: Max 4mA
- Burst Mode Operation
- Internal High Voltage Start-up Switch
- Under Voltage Lockout (UVLO): 12V/8V
- Latch Protection & Soft Start Function
- Over Voltage Protection: 19V
- Operating Frequency up to 300kHz
- Max Duty Cycle: 95%

Typical Applications

- Off-Line Adapter Applications
- Auxiliary Power Supplies

Description

The FAN7601 is a green programmable frequency current mode PWM controller. It is specially designed for the off-line adapter application and the auxiliary power supplies which require high efficiency at a light load and no load. The internal high voltage start-up switch and the burst mode reduce the power loss. The FAN7601 includes some protections such as latch protection and over voltage protection. The latch protection can be used for over voltage protection and/or thermal protection and so on. And the soft start prevents the output voltage over shoot at start up.


10-SSOP   8-SOP   8-DIP

Internal Block Diagram

* ( ) is 10-SSOP PIN Number

Rev. 1.0.2

Pin Assignments

8-DIP, 8-SOP

Vref	Vcc	Out	GND
8	7	6	5

FAN7601

YWW

1	2	3	4
Vstr	CS/FB	Latch/SS	Rt/Ct

10-SSOP

Vref	NC	Vcc	Out	GND
10	9	8	7	6

7601

YWW

1	2	3	4	5
Vstr	NC	CS/FB	Latch/SS	Rt/Ct

Pin Definitions

Pin Number	Pin Name	Pin Function Description
1 (1)	Vstr	Start-up
2 (3)	CS/FB	Current Sense and Feedback
3 (4)	Latch/SS	Latch Protection and Soft Start
4 (5)	Rt/Ct	Oscillator Timing
5 (6)	GND	Ground
6 (7)	Out	Gate Drive Output
7 (8)	V_{CC}	IC Power Supply
8 (10)	V_{ref}	Voltage Reference

*( ) is 10-SSOP PIN Number

Absolute Maximum Ratings

(Ta = 25°C, unless otherwise specified)

Characteristics		Symbol	Value	Unit
Supply Voltage		V_{CC}	20	V
Input Voltage CS/FB		$V_{CS/FB}$	-0.3 to 20	V
Operating Temperature		T_{OPR}	-25 to +125	°C
Storage Temperature		T_{STG}	-55 to +150	°C
Junction Temperature		Tj	150	°C
Output Current		I_O	250	mA
Vstr Input Voltage		Vstr	500	V
ESD Capability, HBM Model (All pins except Vcc and Vstr)		-	2.0	kV
ESD Capability, Machine Model		-	300	V
Thermal Resistance, Junction to Air	8-DIP	Rθja	100	°C/W
	8-SOP		180	
	10-SSOP		130	

Electrical Characteristics

(T_a = -25°C ~ 125°C, Vcc = 14V, Rt = 9.5kΩ, Ct = 2.2nF unless otherwise specified)

Characteristics	Symbol	Conditions	Min.	Typ.	Max.	Unit
REFERENCE SECTION						
Reference Output Voltage	V_{ref}	I_O = 1mA	4.85	5.00	5.15	V
Line Regulation	ΔV_{ref1}	V_{CC} = 10V ~ 18V	-	10	20	mV
Load Regulation	ΔV_{ref2}	I_O = 1mA ~ 10mA	-	20	30	mV
OSCILLATOR SECTION						
Initial Accuracy	F_{OSC}	-	90	100	110	kHz
Voltage Stability	ST_V	V_{CC} = 10V ~ 18V	-	1.0	1.5	%
Amplitude	V_{OCS}	V_{pin4} peak-to-peak	-	1.25	-	V
PWM SECTION						
CS/FB Threshold Voltage1	$V_{CS/FB1}$	-	0.9	1.0	1.1	V
Maximum Duty Cycle	D_{MAX}	Ta = 25°C	92	95	98	%
Minimum Duty Cycle	D_{MIN}	-	-	-	0	%
BURST MODE SECTION						
CS/FB Threshold Voltage2[1]	$V_{CS/FB2}$	-	0.77	0.97	1.17	V
CS/FB Threshold Voltage3[1]	$V_{CS/FB3}$	-	0.7	0.9	1.1	V
SOFT START SECTION						
Soft Start Current	I_{SS}	V_{pin3} = GND	9	12	15	μA
Soft Start Limit Voltage[2]	V_{SL}	I_{SS} = 1μA	1.2	1.5	1.8	V
PROTECTION SECTION						
Latch Voltage	V_{LATCH}	-	2.25	2.5	2.75	V
Over Voltage Protection	V_{OVP}	-	18	19	20	V
UVLO SECTION						
Start Threshold Voltage	V_{tH}	-	11	12	13	V
Minimum Operating Voltage	V_{tL}	-	7	8	9	V
TOTAL CURRENT SECTION						
Operating Supply Current	I_{OP}	-	-	3	4	mA
OUTPUT SECTION						
Low Output Voltage	V_{OL}	Ta =25°C, I_O = 100mA	-	2	2.5	V
High Output Voltage	V_{OH}	Ta =25°C, I_O = -100mA	11.5	12	14	V
Rising Time [1]	T_r	Ta =25°C, CI = 1nF	-	45	150	ns
Falling Time [1]	T_f	Ta =25°C, CI = 1nF	-	35	150	ns
START UP SECTION						
VSTR Start-up Current	I_{str}	V_{str} = 30V, Ta =25°C	0.5	1	1.5	mA

Note:

1. These parameters, although guaranteed, are not 100% tested in production.
2. It is recommended to connect 1MΩ resistor between the Latch/SS pin and GND to prevent abnormal operation of the latch protection by noise coupling.

Typical Performance Characteristics

Figure 1. Trimmed Reference Voltage

Figure 2. Supply Current


Figure 3. Vcc Start Threshold Voltage

Figure 4. Vcc Stop Threshold Voltage

Figure 5. Oscillator Frequency

Figure 6. Maximum Duty Cycle

Typical Performance Characteristics (Continued)

**Figure 7. Oscillator High Threshold Voltage**

Figure 8. Oscillator Low Threshold Voltage

**Figure 9. Output Rising Time**

Figure 10. Output Falling Time

Figure 11. Start-up Current

Figure 12. Over Voltage Protection Level

Typical Performance Characteristics (Continued)

Figure 13. Latch Protection Voltage

Figure 14. Soft Start Current

Figure 15. Oscillator Frequency Characteristic

Mechanical Dimensions

8DIP

9.83 / 9.00

6.67 / 6.096

8   5

1   4

5.08 MAX

3.683 / 3.20

0.33 MIN

2.54

0.56 / 0.355

3.60 / 3.00

1.65 / 1.27

7.62

8.255 / 7.61

7.62

0.356 / 0.20

0° / 15°

9.957 / 7.87

Mechanical Dimensions (Unit: mm) (Continued)

Package

8-SOP

MIN $\frac{0.1 \sim 0.25}{0.004 \sim 0.001}$

$\frac{1.55 \pm 0.20}{0.061 \pm 0.008}$

$\left(\frac{0.56}{0.022}\right)$

#1   #8

#4   #5

$\frac{5.13}{0.202}$ MAX

$\frac{4.92 \pm 0.20}{0.194 \pm 0.008}$

$\frac{0.41 \pm 0.10}{0.016 \pm 0.004}$

$\frac{6.00 \pm 0.30}{0.236 \pm 0.012}$

$\frac{1.80}{0.071}$ MAX

$\frac{1.27}{0.050}$

$\frac{0.15 \substack{+0.10 \\ -0.05}}{0.006 \substack{+0.004 \\ -0.002}}$

$\frac{3.95 \pm 0.20}{0.156 \pm 0.008}$

$\frac{MAX0.10}{MAX0.004}$

$\frac{5.72}{0.225}$

0~8°

$\frac{0.50 \pm 0.20}{0.020 \pm 0.008}$

Mechanical Dimensions (Unit: mm) (Continued)

Package

10-SSOP-225

Ordering Information

Device	Package	Operating Temp.
FAN7601N	8-DIP	
FAN7601M	8-SOP	-25°C ~ 125°C
FAN7601G	10-SSOP	

www.fairchildsemi.com

PUBLICATION ORDERING INFORMATION

© Semiconductor Components Industries, LLC

www.onsemi.com