


Connectors for Copper Conductor

Two-Hole Lugs —
Standard Barrel
600V to 35KV

Material: High-Conductivity
Wrought Copper

Finish: Electro Tin Plate



CAT. NO.	CODE	WIRE SIZE		BOLT SIZE	DIMENSIONS (IN.)							DIE CODE	DIE COLOR
		FLEX CLASS G, H, I, K, M†			A	B	C	D	E	F	G		
54201	#14-10 AWG			¼	1.86	1.19	.50	.05	.20	¼	⅝	ERG2002	YELLOW
256-30695-1302				⅝	2.48	1.81	.56	.04	.22	⅝	1	ERG2002	YELLOW
54204	8 AWG			#10	1.88	1.18	.42	.08	.26	¼	⅝	21	RED
256-31426-33*				#10	1.88	1.18	.41	.06	.26	⅜	⅜	21	RED
256-31426-33PH		23 Navy		#10	1.88	1.18	.41	.06	.26	⅜	⅜	21	RED
542040410		#8 Weld		¼	2.01	1.31	.42	.08	.26	¼	⅝	21	RED
542040416		37/24 = 14.9 kcmil		¼	2.38	1.68	.42	.08	.26	¼	1	21	RED
256-30695-1094				¼	2.50	1.81	.56	.05	.26	¼	⅜	21	RED
256-30695-251				⅝	2.50	1.81	.56	.05	.26	⅝	1	21	RED
256-30695-1070				#12	1.81	1.19	.44	.11	.30	¼	½-⅝	24	BLUE
256-30695-1153	#6 AWG			#10	1.98	1.28	.44	.08	.30	¼	½	24	BLUE
256-30695-1183				#10	1.98	1.19	.44	.08	.30	⅜	⅝-⅜	24	BLUE
54205		30 Navy		¼	1.98	1.28	.44	.08	.30	¼	⅝	24	BLUE
256-30695-1095		#6 Weld		¼	2.13	1.31	.43	.08	.30	¼	⅜	24	BLUE
256-30695-252		61/24 = 24.6 kcmil		¼	2.38	1.63	.43	.08	.30	¼	1	24	BLUE
256-30695-372		133/.014		¼	2.13	1.43	.43	.08	.30	¼	⅜	24	BLUE
256-30695-913				¼	2.38	1.75	.43	.08	.30	¼	1	24	BLUE
256-30695-253				⅝	2.58	1.81	.55	.08	.30	⅝	1	24	BLUE
54206	#4 AWG	40-50 Navy		¼	2.03	1.28	.52	.10	.37	¼	⅝	29	GRAY
256-30695-1184		91/24 = 36.7 kcmil		⅝	2.31	1.63	.52	.10	.37	⅝	1	29	GRAY
256-30695-255		133/.0177, 49/.029		⅝	2.56	1.81	.59	.09	.37	⅝	1	29	GRAY
54207	#2 AWG			¼	2.13	1.28	.59	.11	.41	¼	⅝	33	BROWN
256-30695-1355		60 Navy		¼	2.15	1.31	.59	.13	.41	¼	⅜	33	BROWN
256-30695-1185		125/24 = 50.4 kcmil		¼	2.38	1.53	.59	.11	.41	¼	1	33	BROWN
256-30695-257		#4 Weld		⅝	2.67	1.81	.60	.1	.41	⅝	1	33	BROWN
256-30695-1049				⅝	3.75	2.88	.75	.09	.41	⅝	1¼	33	BROWN
54208	#1 AWG	75 Navy		¼	2.13	1.28	.68	.11	.47	¼	⅝	37	GREEN
256-30695-1233		150/24 = 60.5 kcmil		⅝	2.69	1.62	.69	.13	.47	½	1	37	GREEN
256-30695-1236		175/24 = 70.6 kcmil, 133/.0223		⅝	2.75	1.81	.68	.11	.47	⅝	1	37	GREEN
256-30695-329	1/0 AWG			¼	2.75	1.81	.75	.14	.52	⅝	⅜	42	PINK
54255		100 Navy		⅝	2.56	1.56	.75	.14	.52	⅝	⅝	42	PINK
256-30695-1234		#1 Weld		⅝	2.75	1.78	.75	.14	.52	⅝	1	42	PINK
54209		225/24 = 90.8 kcmil		⅝	2.88	1.93	.75	.13	.52	⅝	1	42	PINK
256-30695-1265		133/.0254		⅝	3.50	2.57	.75	.14	.52	⅝	1¼	42	PINK
256-30695-886				½	3.78	2.83	.75	.13	.52	½	1¼	42	PINK
256-30695-1175	2/0 AWG	125 Navy		¼	2.45	1.44	.83	.14	.57	¼	⅜	45	BLACK
54261		1/0 Weld		⅝	2.70	1.63	.83	.14	.57	⅝	⅝	45	BLACK
256-30695-832		275/24 = 111 kcmil		⅝	2.88	1.81	.81	.14	.57	⅝	1	45	BLACK
54210		133/.0282		⅝	2.93	1.93	.83	.13	.57	⅝	1	45	BLACK
54260				½	3.83	2.81	.83	.14	.57	⅝	1¼	45	BLACK
54266	3/0 AWG	150 Navy, 2/0 Weld		⅝	2.88	1.75	.94	.14	.63	⅝	1	50	ORANGE
54211		325/24 = 131 kcmil		⅝	2.94	1.81	.94	.14	.63	⅝	1	50	ORANGE
54265		133/.0316, 259/.0227, 427/.0177		½	3.94	2.81	.94	.14	.63	½	1¼	50	ORANGE

† Contact Technical Services for specific stranding listings

Tooling: pp. B76-B92

Die Selector Chart: pp. B93-B95

* Blind End

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Canada
Tel: 450.347.5318
Fax: 450.347.1976

Technical Services
Tel: 888.862.3289

Thomas & Betts
www.tnb.com