

FEATURES

- High reliability
- Small size with high dielectric constant
- Low inductance
- Popular temperature coefficients available
- Wide operating temperature range
- High insulation resistance
- Case sizes: 0603, 0805, 1206, 1210



CHARACTERISTICS

Item	Characteristics		
	NPO / COG	X7R	Z5U
Operating Temperature Range	-55°C ~ +125°C	-55°C ~ +125°C	-25°C ~ +85°C
Temperature Coefficient	±30ppm/°C for C>20pF +120ppm, -40ppm/°C for C≤20pF	ΔC ±15% maximum over -55°C +125°C	ΔC ±56%-22% maximum over +10°C +85°C
Measuring Conditions for Capacitance and D.F.	1MHz, 1Vrms for C≤1,000pF 1KHz, 1Vrms for C>1,000pF	1KHz, 1Vrms	1KHz, 0.3Vrms
Dissipation Factor and Tangent of Loss Angle (Tan δ)	≥0.001 for C≥50pF ≤1.5(150/C + 7) × 10 ⁻² for C<50pF	≤0.025	≤0.030
Insulation Resis. After 60 sec. Charging at Rated Voltage 25°C	≥100GΩ or ≥1,000MΩ(C) whichever is less	≥100GΩ or ≥1,000MΩ(C) whichever is less	≥10GΩ or ≥1,000MΩ(C) whichever is less
Voltage Test 25°C	2.5 x rated voltage	2.5 x rated voltage	2.5 x rated voltage
Capacitance Aging	0	=1.5% per decade hour	=5% per decade hour

PART NUMBERING SYSTEM

C	C	5	0	2	N	1	0	1	J	/	R	E	E	L
Series		Voltage		Case Size	Temperature Coefficient	Value		Tolerance	Suffix					

CODES FOR CASE SIZE, TEMPERATURE COEFFICIENT, AND TOLERANCE

Case Size	Code
0805	1
1206	2
1210	3
0603	4

Temperature Coefficient	Code
NPO / COG	N
X7R	B
Z5U	Z
Y5V	V

Tolerance	Code
±0.25pF	C
±0.5pF	D
±5%	J
±10%	K

For capacitance values below 10pF, use C or D.
GMV = Guaranteed Minimum Value

Suffix	Code
Tape and Reel	/REEL
Bulk	-BK

CAPACITANCE RANGES


Case Size	NPO / COG		X7R		Z5U (0805, 1206, 1210) / Y5V (0603)	
	50V	100V	50V	100V	50V	100V
0603	1.0pF~470pF		100pF~0.01μF		0.01μF~0.1μF	---
0805	1.0pF~1500pF	1.0pF~1000pF	100pF~0.1μF	100pF~.022μF	2700pF~0.15μF	---
1206	1.0pF~3900pF	1.0pF~2700pF	100pF~0.1μF	100pF~.047μF	8200pF~0.47μF	---
1210	4700pF~8200pF	3300pF~5600pF	0.12μF~0.22μF	.047μF~0.1μF	0.22μF~0.68μF	---

TOLERANCE AVAILABLE

Availability	NPO / COG				X7R			Z5U		
Tolerance	±0.25pF	±0.5pF	±2%	±5%	±5%	±10%	±20%	±20%	+80% -20%	+100% -0%
Capacitance	<5pF	≤10pF	>13pF	≥10pF	All Values	All Values	All Values	All Values	All Values	All Values



DIMENSIONS



Case Size	Dimensions (mm)			
	L (length)	W (width)	T (thickness) max.	E (termination)
0603	1.52 ± 0.2	0.8 ± 0.2	.65	0.5 ± 0.2
0805	2.0 ± 0.2	1.2 ± 0.2	1.0	0.5 ± 0.2
1206	3.2 ± 0.2	1.6 ± 0.2	1.25	0.5 ± 0.2
1210	3.2 ± 0.2	2.5 ± 0.2	1.3	0.5 ± 0.2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

<u>140-CC502B683K</u>	<u>140-CC502B332K</u>	<u>140-CC502B822K</u>	<u>140-CC502Z683M</u>	<u>140-CC502B392K</u>	<u>140-CC502B561K</u>
<u>140-CC501B822K</u>	<u>140-CC501B103K</u>	<u>140-CC502B391K</u>	<u>140-CC502B821K</u>	<u>140-CC501B104K</u>	<u>140-CC502B183K</u>
<u>140-CC501B123K</u>	<u>140-CC502B153K</u>	<u>140-CC502B472K</u>	<u>140-CC501B221K</u>	<u>140-CC502B473K</u>	<u>140-CC501B222K</u>
<u>140-CC501B183K</u>	<u>140-CC502B682K</u>	<u>140-CC502B333K</u>	<u>140-CC502B222K</u>	<u>140-CC501B182K</u>	<u>140-CC501B472K</u>
<u>140-CC502B471K</u>	<u>140-CC501B331K</u>	<u>140-CC501B152K</u>	<u>140-CC502B562K</u>	<u>140-CC501B821K</u>	<u>140-CC501B122K</u>
<u>140-CC502B393K</u>	<u>140-CC501B273K</u>	<u>140-CC502B223K</u>	<u>140-CC501B272K</u>	<u>140-CC502B681K</u>	<u>140-CC501B332K</u>
<u>140-CC501B153K</u>	<u>140-CC255B103K</u>	<u>140-CC501B473K</u>	<u>140-CC501B102K</u>		