




LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
		J		REVISED PER ECR-12-013459	27NOV2012	KH PD


- 1 CONTINUOUS STRIP ON REELS.
- 2 MATING TAB THK TO BE 0.81±0.025 [.032±.001].
- 3 WIRE SIZE IS #18-#14 AWG.
- 4 INSULATION RANGE IS 1.52-3.81 [.060-.150] DIA.
- 5 REEL WITH INTERLEAVING PAPER.
- 6 MATERIAL: BRASS
- 7 MATERIAL: HO4 PHOS BRZ
- 8 RECEPTACLE LENGTH CAN VARY UP TO 6.35 [.250] MAX, THIS SIDE ONLY.
- 9 PREPRODUCTION - FASR REQUIRED




VIEW A-A



SECTION B-B




SECTION C-C



PART NO.	WIRE		INSULATION DIAMETER (MAX)	WIRE BARREL CRIMP				TENSILE STRENGTH POUNDS
	QTY	SIZE AWG		WIDTH	CRIMP HEIGHT	CRIMPER	ANVIL	
63314-1	1	14	.150	.120	.071	F	FLAT	50
	1	16			.063			30
	1	18			.057			20

5 REVERSE REELED	7	SILVER	9 63314-5
	6	TIN	63314-4
	6	TIN	63314-2
	6	—	63314-1
	MATERIAL	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	JR RUTH	6/16/87	 TE Connectivity			
			CHK	MS FEHER	6/16/87				
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD	C MEYERS	6/16/87	NAME		
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE, FLAG, FASTON, 6.35 [.250] SERIES			
		1 PLC ± -		—					
		2 PLC ± 0.25 [.010]		—					
		3 PLC ± -		APPLICATION SPEC					
		4 PLC ± -		—		SIZE			
		ANGLES ± ±				CAGE CODE			
MATERIAL		FINISH		WEIGHT		DRAWING NO			
—		SEE TABLE		—		RESTRICTED TO			
CUSTOMER DRAWING						A2 00779 C-63314			
						SCALE			
						7:1			
						SHEET			
						1 of 1			
						REV			
						J			