




ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	31.0	± max
T:	7.0	± max
Lead Diameter	1.0	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	4.0	± max
B:	7.80	± nom
C:	4.50	± nom



Electrical Specifications

Resistance:	0.5	Ω	± 25 %
Max Steady State Current upto 65°C:	40.00	A	
Max Rec. Energy Rating:	250	J	
Actual Failure Instantaneous Energy:	400	J	
Maximum Capacitance @ 120 VAC:	13,500	μf	
Maximum Capacitance @ 240 VAC:	4,341	μf	
Maximum Capacitance @ 440 VAC:	1,003	μf	
Maximum Capacitance @ 680 VAC:	500	μf	
Resistance @ 100% Max Current:	0.01	Ω	
Resistance @ 50% Max Current:	0.01	Ω	
Body Temperature at 100% Max Current:	224.00	°c	
Dissipation Constant:	79.8	mw/°c	
Thermal Time Constant:	194	Sec.	
Material Type (for Beta and Curve):	A		

MS32 0R540

Date: 11/11/2008

Drawn by: Erin Landis

Ametherm, Inc.
3111 N. Deer Run Road
Carson City, Nevada USA 89701
www.ametherm.com

Approved By: Mehdi Samii

Revision: a

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[MS32 0R540](#)