


| REVISIONS |      |                              |
|-----------|------|------------------------------|
| ISS       | ZONE | DESCRIPTION\PER REQUEST\DATE |
|           |      |                              |



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
  2. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  3. BERYLLIUM COPPER PER QQ-C-530
  4. GOLD PL. 50 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  5. TEFLON MIL-P-19468

| 6   | CONTACT PIN   | NOTE 3   | NOTE 4  | 1    | SMAF-RSMAF-6    |
|-----|---------------|----------|---------|------|-----------------|
| 5   | GASKET        | SILICONE | RED     | 1    | GS-6/43X06      |
| 4   | RETAINER RING | NOTE 3   | NATURAL | 1    | SMA5000-4-B     |
| 3   | INSULATOR     | NOTE 5   | NATURAL | 2    | SMA5071A1-3T-50 |
| 2   | BODY          | NOTE 1   | NOTE 2  | 1    | SMA5071A1-2-B   |
| 1   | SHELL         | NOTE 1   | NOTE 2  | 1    | SMA5000-1-C     |
| NO. | DESCRIPTION   | MATERIAL | FINISH  | Q'TY | DRAWING NO.     |

| DIMENSIONS ARE IN MILLIMETERS         |  |  |  |  | PART NO.                    |      |
|---------------------------------------|--|--|--|--|-----------------------------|------|
| UNLESS OTHERWISE SPECIFIED TOLERANCES |  |  |  |  | TITLE                       |      |
| 0.5-6 = ±0.2                          |  |  |  |  | APPROVED                    | DATE |
| 6-30 = ±0.4                           |  |  |  |  | CHECKED                     | DATE |
| 30-120 = ±0.6                         |  |  |  |  | DRAWN                       | DATE |
| 120-315 = ±1                          |  |  |  |  | DRAWING NO.                 |      |
| 315-1000 = ±1.6                       |  |  |  |  | FILE NO.                    |      |
| 1000-2000 = ±2.4                      |  |  |  |  | F:\DWG\SMAF\RSMAF\50\3GT50G |      |

# Amphenol-Kai Jack

TAIAN TAIWAN

SMA FEMALE TO SMA REVERSE POLARITY FEMALE ADAPTOR

KJ-SMAF-RSMAF-3GT50G-50