


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2070	A	Released	JN	09-03-09	JWM	09-03-09	JWM	09-03-09



Specification

1. Rated Noise Power: 0.15 W
2. Max. Input Power: 0.3 W
3. Rated Frequency Range: 700~5000Hz
4. Rated Frequency: 1200 ± 200 Hz
5. Rated Impedance: 8Ω
6. Min Sound Pressure Level: 70dB at 1.2KHz
 - 1.1 Vrms Sine Wave/10cm
7. Case Material: ABS
8. Operating Temperature: -20~+60°C
9. Weight: 12g

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:
Jason Nash
DATE:
09-03-09
CHECKED BY:
Jason Nash
DATE:
09-03-09
APPROVED BY:
Jason Nash
DATE:
09-03-09

DRAWING TITLE:
MECHANICAL BUZZER
SIZE DWG. NO. ELECTRONIC FILE REV
A MCKPMB-G2300-K3902 25R0737.dwg A
SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1