





PRODUCT NO.
SEE TABLE



SECTION Y-Y

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family HEADERS							
ltr		ecn no		dr		date		tolerances unless otherwise specified				title					
A		V71646		SAR		12/15/97		angles		linear		.XX±.01/.3		INCH/MM		HEADER, SLIM-LINE	
B		V81270		SAR		8/5/98						.xxx±.005/.13		scale 1:1		VERTICAL ASS'Y, 2-WALL	
C		V94352		DAI		11/17/99		0'±2'				.xxxx±.0020/.051					
D		M05-0089		ERE		5/20/05		dr		S. ROYER		12/15/97				dwg no	
E		M07-0116		AGS		2/25/07		enrg		L. FYE		12/15/97				sheet 1 of 2	
								chr		L. FYE		12/15/97				size	
								appd		L. FYE		12/15/97				A3	
sheet index		revision sheet		E		E										type	
1		2														Product Customer Drawing	

PRODUCT NO.

74374 - F ZZ Y LF

F	PLATING NOTE 10
1	30μ / 0.76μm GOLD
5	30μ / 0.76μm GXT

NO. OF PINS ZZ	POSITIONS	DIM B	DIM C
10	2 X 5	.630/16.00	.400/10.16
14	2 X 7	.830/21.80	.600/15.24
26	2 X 13	1.430/35.60	1.200/30.48
34	2 X 17	1.830/46.48	1.600/40.64
40	2 X 20	2.130/54.10	1.900/48.26

Y	DIM D TAIL LENGTH
2	.120/3.05

LEAD FREE OPTION
NOTE 7

NOTES:

- ① PLASTIC MATERIAL: 30% GLASS FILLED, BLACK PCT
FLAME RETARDANT PER UL-94-V0
- ② PIN MATERIAL: PHOS BRONZE.
3. 4 LBS/1.8 KG MIN PIN RETENTION.
- ④ PIN CONTACT SURFACE IS TO BE FREE OF BURRS,
SCRATCHES AND PLASTIC DEBRIS.
5. PACKAGING: ADD 'T' TO THE END OF THE 4-DIGIT DASH NO.
TUBE PACKAGING. [ex 74374-1402T]
6. PART NUMBERS WITH "R" FOLLOWING THE DASH NUMBER
WILL HAVE RETENTIVE TAILS. [ex 74374-1402TR]
TWO PAIR OF PINS LOCATED APPROXIMATELY IN THE CENTER
OF 2X14 AND SMALLER SIZE ARE TO BE KINKED.
TWO PAIR OF PINS LOCATED ON EACH END OF 2X15 AND LARGER
ARE TO HAVE 2 PAIR OF PINS KINKED ON EACH END.
- ⑦ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- ⑨ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑩ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 1:1	title
E					angles linear .XX±.01/.3 0°±2° .xxx±.005/.13 .xxxx±.0020/.051		HEADER, SLIM-LINE VERTICAL ASS'Y, 2-WALL
			dr	S. ROYER	12/15/97		dwg no
			enrg	L. FYE	12/15/97		sheet2 of 2
			chr	L. FYE	12/15/97		size A3
			appd	L. FYE	12/15/97		type Product Customer Drawing
sheet index	revision sheet						

form: A3