



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED TO PRODUCTION	8/27/01	R. CARRICK
B	ECN# 1628: ADDED COMPONENT SPECIFICATION TABLE	12/31/03	T. CLARK
C	ECN# 2731 - ADDED ROHS STAMP	10/23/07	D. GRIFFIN
.	.	.	.



MALE 24-CONTACT  
GPIB CONNECTOR



FEMALE 24-CONTACT  
GPIB CONNECTOR



2X ISO M3.5 X 0.6  
THREAD

**NOTES:**

- NOTES:  
1. WIRED STRAIGHT THROUGH PER ANSI/IEEE STD 488.1-1987.  
2. TWO DUST CAPS PROVIDED WITH ADAPTOR.

**MATERIAL:**

HOUSING: DIE-CAST ALUMINUM ALLOY  
CONNECTOR INSULATORS: GLASS-FILLED PBT, BLUE, UL94-V0 RATED  
CONNECTOR CONTACTS: 24, COPPER ALLOY, RIBBON, .085" PITCH  
SCREWLOCKS: STEEL

**FINISH:**

HOUSING: NICKEL PLATED  
CONNECTOR CONTACTS: 30μ INCHES GOLD PLATED OVER NICKEL  
SCREWLOCKS: BLACK OXIDE

**ELECTRICAL:**

VOLTAGE RATING: 200 VOLTS  
CURRENT RATING: 1A PER CONTACT AT 25°C  
INSULATION RESISTANCE: 1 GΩ

**ENVIRONMENTAL:**

OPERATIONAL TEMPERATURE  
RANGE: -40°C TO +85°C

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] TOLERANCES TO BE: .X ±.1 [2.5] ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 > 60 [1524] +5% / -0%	APPROVALS	DATE	L-com CONNECTIVITY PRODUCTS				45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY RON CARRICK	8/27/2001	CATEGORY		IEEE-488 GPIB			
	CHECKED BY DOUG PARHAM	8/27/2001	PRODUCT DESCRIPTION		IEEE-488 REVERSING EXTENDER, M/F			
	APPROVED BY C. MCCORMICK	8/27/2001	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CIB24XR</b>	REV. <b>C</b>		
PROJ 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SCALE: NONE		CAD FILE: CIB24XR.SLDDRW		SHEET 1 OF 1	