

Product data sheet

Characteristics

XS508BSCAL08M12

inductive sensor XS5 M8 - L33mm - stainless - Sn1.5mm - 12..24VDC - M12

Price* : 99.87 USD



(!) Discontinued

Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Device application	-
Sensor name	XS5
Sensor design	Cylindrical M8
Size	33 mm
Body type	Fixed
Detector flush mounting acceptance	Flush mountable
Material	Metal
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	0.06 in (1.5 mm)
Discrete output function	1 NO
Output circuit type	DC
Electrical connection	4 pins M12 remote male connector 1-4
Cable length	2.62 ft (0.8 m)
[Us] rated supply voltage	12...24 V DC reverse polarity protection
Switching capacity in mA	1.5...100 mA DC overload and short-circuit protection
IP degree of protection	IP67 IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Thread type	M8 x 1
Detection face	Frontal
Front material	PPS
Enclosure material	Nickel plated brass
Operating zone	0.00...0.05 in (0...1.2 mm)
Differential travel	1...15% of Sr
Cable composition	2 x 0.11 mm ²
Wire insulation material	PvR

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Status LED	Output state 1 LED yellow)
Supply voltage limits	10...36 V DC
Maximum residual current	0.5 mA open state
Switching frequency	<= 4000 Hz
Maximum voltage drop	<4 V closed)
Maximum delay first up	10 ms
Maximum delay response	0.2 ms
Maximum delay recovery	0.2 ms
Marking	CE
Threaded length	0.98 in (25 mm)
Height	0.31 in (8 mm)
Length	1.30 in (33 mm)
Net weight	0.19 lb(US) (0.085 kg)

Environment

Product certifications	CSA UL
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Vibration resistance	25 gn +/- 2 mm 10...55 Hz)IEC 60068-2-6
Shock resistance	50 gn 11 ms IEC 60068-2-27

Ordering and shipping details

Category	22486-SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	03389119045971
Package weight(Lbs)	0.11 lb(US) (0.050 kg)
Returnability	No
Country of origin	FR


Packing Units

Package 1 Height	1.300 dm
Package 1 width	0.410 dm
Package 1 Length	0.940 dm

Contractual warranty


Warranty	18 months
----------	-----------

Dimensions




Minimum Mounting Distances

Side by side




$e (1) \geq 3 \text{ mm/0.12 in.}$

Face to face



$e (2) \geq 18 \text{ mm/0.71 in.}$

Facing a metal object




$e (3) \geq 4.5 \text{ mm/0.18 in.}$

Wiring Schemes

2-Wire Polarised

M12 connector



NO output



Performance Curves

Standard Steel Target : 8x8x1 mm

