


THERMOFIT • SPECIFICATION CONTROL DRAWING • MOLDED PARTS

1. All dimensions are in inches; all angles are in degrees.
2. Dimensions appearing in table below are as follows:
a - As supplied b - After unrestricted recovery
3. Weight shown in table of dimensions is based on polyolefin part.
4. Molding ports are optional. When specified, they will be located as shown. Order 323A211-3-00 when molding ports are required.

If this document is printed it becomes uncontrolled.
Check for the latest revision.



Mat. No.	Description	Rayclad Matl. Spec.	Specific Grav. Max.
3	Polyolefin	RT 301	1.40
4	Flex Poly	RT 304	1.40
25	Elastomer, fluid resistant	RT 1325	

Add material number as suffix to part number;
Example - Order 323A211-3 when polyolefin is required.

TABLE OF DIMENSIONS

PART NO.	H		J & K		P		R		S		T		U		JO & KO		W		C	
	Min a	Max b	Min a	Max b	a	±10% b	a	±10% b	a	±10% b	a	±20% b	a	±20% b	a	±10% b	a	±20% b	±10° a	±5° b
323A211-	1.73	.65	1.00	.26	—	1.60	—	.54	—	.45	—	.09	—	.03	—	.29	—	.06	150	90
PART NO.	Weight lbs ±10%																			
323A211-	.006																			

Raychem

E.O.

REV. DATE
A 8/71

DESCRIPTION
Flex Poly added.

DRN

DD

PART DESCRIPTION

PART NO.

REV LTR

CHK'D

KT

BOOT, T, WITH LIP

323A211

B

AUTH

RAP

AUTH

HOP

DATE
November 21, 1983