




DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



⚠ OBSOLETE

OBSOLETE
⚠

⚠ OBSOLETE

WIRE RANGE :
0,3-0,56 mm
INSULATION RANGE :
1,0-2,0 DIA.

6-160303-3	PRE-TIN HOT DIP	PHOSPHORBRONZE	6-160321-3
6-160303-2	TIN-LEAD	BRASS	6-160321-2
6-160303-0	PRE-TIN HOT DIP	PHOSPHORBRONZE	6-160321-0
5-160303-9	PRE-TIN HOT DIP	BRASS	5-160321-9
5-160303-6	TIN	PHOSPHORBRONZE	5-160321-6
5-160303-4	GOLD	BRASS	5-160321-4
5-160303-3	SILVER	BRASS	5-160321-3
5-160303-2	TIN	BRASS	5-160321-2
5-160303-1	NONE	BRASS	5-160321-1
MAKE FROM STRIP PN		FINISH	MATERIAL
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
AI	ECO-10-000030	KK	AEG 04JAN10
A	EH-0243-94	DK	PB 11-04-94
LTR.	REVISION RECORD	DR.	CHK. DATE
DR.:	D.KESSLER	CHK.:	P.BEIJNON
DATE:	11-04-94	DATE:	-
APP.:	L.V.SOEST	DATE:	-
DWG. No.		SHEET	
C-160321		1 OF 1	
REV. LTR.		AI	

CUSTOMER DRAWING FOR REFERENCE ONLY
WILL NOT BE UPDATED

© COPYRIGHT 19 - BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.

THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION - , 19 -

Tyco Electronics AMP ITALIA S.r.l.
Corso F.lli Cervi, 15
COLLEGNO (TORINO)

NAME
.110 SRS FASTON RECEPTACLE
LOOSE PIECES

DWG. No. C-160321
SHEET 1 OF 1
REV. LTR. AI