


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A7	REVISED PER ECO-15-003872	25MAR2015	DD	DS



- ⚠ ACCEPTS #3 SELF TAPPING THREAD FORMING SCREWS OR METRIC EQUIVALENT. DRIVE TO 0.6-0.8 N-m.
- ⌚ DATE CODE TO BE BRANDED IN THIS LOCATION PER TE SPEC 102-60. FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK LAST DIGIT = DAY.
- 📦 MATERIALS: HEADER HOUSING - GLASS FILLED PBT
PINS - TIN OR GOLD PLATED BRASS
- 🔑 HOUSING COLORS ARE MECHANICALLY KEYED TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.
5. HEADER MATES TO PLUG ASSEMBLY 776273 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854

776261-1 & 1-776261-1 SHOWN

BLUE	DURAGOLD	1-776261-5
GRAY	DURAGOLD	1-776261-4
NATURAL	DURAGOLD	1-776261-2
BLACK	DURAGOLD	1-776261-1
BLUE	TIN	776261-5
GRAY	TIN	776261-4
NATURAL	TIN	776261-2
BLACK	TIN	776261-1
HEADER COLOR	PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. STRAUSSER 04FEB2010	NAME	
DIMENSIONS:		CHK D. STRAUSSER 22MAR2010	PRODUCT SPEC	
mm		APVD D. STRAUSSER 27APR2010	APPLICATION SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-1329	114-16016	
0 PLC ±.2		108-1329	114-16016	
1 PLC ±0.13		108-1329	114-16016	
2 PLC ±.1		108-1329	114-16016	
3 PLC ±.1		108-1329	114-16016	
4 PLC ±.1		108-1329	114-16016	
ANGLES ±.5°		108-1329	114-16016	
FINISH		108-1329	114-16016	
MATERIAL		108-1329	114-16016	
3		108-1329	114-16016	
3		108-1329	114-16016	
CUSTOMER DRAWING		108-1329	114-16016	
SCALE		108-1329	114-16016	
4:1		108-1329	114-16016	
SHEET		108-1329	114-16016	
1		108-1329	114-16016	
OF		108-1329	114-16016	
2		108-1329	114-16016	
REV		108-1329	114-16016	
A7		108-1329	114-16016	

-AMPSEAL HEADER4805 (3/13)