


# EUAA18-6.7458M



## ELECTRICAL SPECIFICATIONS


|                               |   |
|-------------------------------|---|
| Nominal Frequency             | 6.7458MHz   |
| Frequency Tolerance/Stability | $\pm 50\text{ppm}$ at 25°C, $\pm 100\text{ppm}$ over 0°C to +70°C |
| Aging at 25°C                 | $\pm 5\text{ppm/year}$ Maximum                                    |
| Load Capacitance              | 18pF Parallel Resonant  |
| Shunt Capacitance (C0)        | 7pF Maximum   |
| Equivalent Series Resistance  | 50 Ohms Maximum   |
| Mode of Operation             | AT-Cut Fundamental  |
| Drive Level                   | 2mWatts Maximum   |
| Storage Temperature Range     | -40°C to +125°C   |
| Insulation Resistance         | 500 Megaohms Minimum at 100Vdc                                    |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                       |
|------------------------------|---------------------------------------|
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C |
| Lead Integrity               | MIL-STD-883, Method 2004              |
| Lead Termination             | Sn 2 $\mu\text{m}$ - 6 $\mu\text{m}$  |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C  |
| Resistance to Soldering Heat | MIL-STD-202, Method 210               |
| Resistance to Solvents       | MIL-STD-202, Method 215               |
| Solderability                | MIL-STD-883, Method 2003              |
| Temperature Cycling          | MIL-STD-883, Method 1010              |
| Vibration                    | MIL-STD-883, Method 2007, Condition A |


# EUAA18-6.7458M

## MECHANICAL DIMENSIONS (all dimensions in millimeters)



| LINE | MARKING                                       |
|------|---|
| 1    | ECLIPTEK                                      |
| 2    | E6.7458M<br><i>E=Configuration Designator</i> |
| 3    | XX<br><i>XX=Ecliptek Manufacturing Code</i>   |


## Recommended Solder Reflow Methods



### High Temperature Solder Bath (Wave Solder)

|  |                                      |
|--|--------------------------------------|
| <b>Ts MAX to Tl (Ramp-up Rate)</b>         | 3°C/second Maximum                   |
| <b>Preheat</b>                             |                                      |
| - Temperature Minimum (Ts MIN)             | 150°C                                |
| - Temperature Typical (Ts TYP)             | 175°C                                |
| - Temperature Maximum (Ts MAX)             | 200°C                                |
| - Time (ts MIN)                            | 60 - 180 Seconds                     |
| <b>Ramp-up Rate (Tl to Tp)</b>             | 3°C/second Maximum                   |
| <b>Time Maintained Above:</b>              |                                      |
| - Temperature (Tl)                         | 217°C                                |
| - Time (tL)                                | 60 - 150 Seconds                     |
| <b>Peak Temperature (Tp)</b>               | 260°C Maximum for 10 Seconds Maximum |
| <b>Target Peak Temperature (Tp Target)</b> | 250°C +0/-5°C                        |
| <b>Time within 5°C of actual peak (tp)</b> | 20 - 40 seconds                      |
| <b>Ramp-down Rate</b>                      | 6°C/second Maximum                   |
| <b>Time 25°C to Peak Temperature (t)</b>   | 8 minutes Maximum                    |
| <b>Moisture Sensitivity Level</b>          | Level 1                              |

## Recommended Solder Reflow Methods



### Low Temperature Solder Bath (Wave Solder)

|  |   |
|--|---|
| <b><math>T_s</math> MAX to <math>T_L</math> (Ramp-up Rate)</b> | 5°C/second Maximum                                    |
| <b>Preheat</b>   |   |
| - Temperature Minimum ( $T_s$ MIN)                             | N/A   |
| - Temperature Typical ( $T_s$ TYP)                             | 150°C   |
| - Temperature Maximum ( $T_s$ MAX)                             | N/A   |
| - Time ( $t_s$ MIN)  | 30 - 60 Seconds                                       |
| <b>Ramp-up Rate (<math>T_L</math> to <math>T_p</math>)</b>     | 5°C/second Maximum                                    |
| <b>Time Maintained Above:</b>                                  |   |
| - Temperature ( $T_L$ )  | 150°C   |
| - Time ( $t_L$ )   | 200 Seconds Maximum                                   |
| <b>Peak Temperature (<math>T_p</math>)</b>                     | 245°C Maximum   |
| <b>Target Peak Temperature (<math>T_p</math> Target)</b>       | 245°C Maximum 1 Time / 235°C Maximum 2 Times          |
| <b>Time within 5°C of actual peak (<math>t_p</math>)</b>       | 5 seconds Maximum 1 Time / 15 seconds Maximum 2 Times |
| <b>Ramp-down Rate</b>  | 5°C/second Maximum                                    |
| <b>Time 25°C to Peak Temperature (t)</b>                       | N/A   |
| <b>Moisture Sensitivity Level</b>                              | Level 1   |

### Low Temperature Manual Soldering

185°C Maximum for 10 seconds Maximum, 2 times Maximum.

### High Temperature Manual Soldering

260°C Maximum for 5 seconds Maximum, 2 times Maximum.