




ELECTRICAL SPECS:

1. LIFE: 10,000 INSERTION/WITHDRAWAL CYCLE MINIMUM
2. CONTACT RESISTANCE: 50mU MAXIMUM
3. INSULATION RESISTANCE: 1000mU MINIMUM
4. DIELECTRIC WITHSTANDING VOLTAGE: 500AC MAXIMUM
5. MAXIMUM RATING: 5A, 12V DC



PANEL CUT-OUT

ROHS COMPLIANT

Date	SYM	REVISION RECORD	AUTH	DR	CK
05/08/04	A	ADDED ELECTRICAL SPECS	T.B.	B.S.	
12/05/08	B	ADDED "ROHS COMPLIANT"	T.B.	B.S.	

ITEM NO.	PART NAME	MATL. SPECIFICATION	Tolerance (Inches)	Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735		
1	HEX. NUT	BRASS, NICKLE PLTD.	Decimal ±.5 (.020)		Scale	Drawn By B.S.
2	FLAT WASHER	IRON, NICKLE PLTD.				Approved By T.B.
3	TOP HOUSING	BRASS, NICKLE PLTD.		Fractional ± .8 (.030)	Title DC JACK - CHASSIS MOUNT, OPEN CIRCUIT	
4	PIN (Ø2.1)	COPPER, NICKLE PLTD.				
5	SOLDER TERMINAL	BRASS, SILVER PLTD.	Angular ± 3°		Date 12/05/08	Drawing Number EJ501A
6	SOLDER TERMINAL	BRASS, SILVER PLTD.				
7	BOTTOM HOUSING	NYLON, BLACK				