



SAFETY DATA SHEET WD40 AEROSOL

According to Regulation (EC) No 1907/2006

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME WD40 AEROSOL
APPLICATION Anti-squeak. Moisture repellant. Releasing agent
SUPPLIER WD40 Company Limited
PO Box 440
Kiln Farm
Milton Keynes
MK11 3LF
Tel: 01908 555400
Fax: 01908 266900
info@wd40.co.uk
EMERGENCY TELEPHONE 00 44 1908 555 400 (08.00 - 16.30)

2 HAZARDS IDENTIFICATION

Flammable. Repeated exposure may cause skin dryness or cracking.

CLASSIFICATION R10, R66.

ENVIRONMENT

The product is not expected to be hazardous to the environment.

PHYSICAL AND CHEMICAL HAZARDS

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

HUMAN HEALTH

See section 11 for additional information on health hazards. This substance has no evidence of carcinogenic properties.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
CARBON DIOXIDE	204-696-9	124-38-9	1-5%	-
PETROLEUM DISTILLATE	265-150-3	64742-48-9	60-80%	Xn;R65. R10,R66.

The Full Text for all R-Phrases are Displayed in Section 16

4 FIRST-AID MEASURES

INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION

DO NOT INDUCE VOMITING! NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Immediately rinse mouth and drink plenty of water (200-300 ml). Get medical attention.

SKIN CONTACT

Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention promptly if symptoms occur after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Use: Foam. Water spray, fog or mist. Dry chemicals, sand, dolomite etc.

SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed or cooled with water. Avoid water in straight hose stream; will scatter and spread fire.

WD40 AEROSOL**UNUSUAL FIRE & EXPLOSION HAZARDS**

Aerosol cans may explode in a fire.

SPECIFIC HAZARDS

Fire or high temperatures create: Carbon monoxide (CO). Carbon dioxide (CO₂).

PROTECTIVE MEASURES IN FIRE

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

6 ACCIDENTAL RELEASE MEASURES**PERSONAL PRECAUTIONS**

Wear protective clothing as described in Section 8 of this safety data sheet.

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb with inert, damp, non-combustible material, then flush area with water.

7 HANDLING AND STORAGE**USAGE PRECAUTIONS**

Read and follow manufacturer's recommendations. Keep away from heat, sparks and open flame. Avoid inhalation of vapours/spray and contact with skin and eyes. Wash hands after handling.

STORAGE PRECAUTIONS

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m ³	ST - ppm	ST - mg/m ³
CARBON DIOXIDE			Asphyxiating		Asphyxiating

PROTECTIVE EQUIPMENT**ENGINEERING MEASURES**

Provide adequate ventilation.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved chemical safety goggles where eye exposure is reasonably probable.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Promptly remove any clothing that becomes contaminated. Wash promptly if skin becomes contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid Aerosol		
COLOUR	Light (or pale) Amber		
ODOUR	Characteristic		
SOLUBILITY	Insoluble in water		
RELATIVE DENSITY	0.817 @ 21°C	VAPOUR DENSITY (air=1)	> 1
VAPOUR PRESSURE	95-105 psi @ 21°C	VOLATILE BY VOL. (%)	57%
FLASH POINT (°C)	44°C TOC (Tag open cup).	FLAMMABILITY LIMIT - LOWER(%)	0.6%
FLAMMABILITY LIMIT - UPPER(%)	8.0%		

10 STABILITY AND REACTIVITY**STABILITY**

Stable under normal temperature conditions and recommended use.

WD40 AEROSOL**CONDITIONS TO AVOID**

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

HAZARDOUS DECOMPOSITION PRODUCTS

During fire, toxic gases (CO, CO₂) are formed.

11 TOXICOLOGICAL INFORMATION**INHALATION**

Vapours may cause headache, fatigue, dizziness and nausea.

SKIN CONTACT

Repeated exposure may cause skin dryness or cracking.

EYE CONTACT

Spray and vapour in the eyes may cause irritation and smarting.

Other Health Effects

This substance has no evidence of carcinogenic properties.

12 ECOLOGICAL INFORMATION**ECOTOXICITY**

The product contains substances which contribute to global warming (greenhouse effect).

BIOACCUMULATION

The product contains potentially bioaccumulating substances.

DEGRADABILITY

The product is easily biodegradable.

13 DISPOSAL CONSIDERATIONS**DISPOSAL METHODS**

Dispose of waste and residues in accordance with local authority requirements. Make sure containers are empty before discarding (explosion risk). Recover and reclaim or recycle, if practical.

14 TRANSPORT INFORMATION

UK ROAD CLASS	2.1		
PROPER SHIPPING NAME	AEROSOLS		
UN NO. ROAD	1950	UK ROAD PACK GR.	#
ADR CLASS NO.	2.1	ADR CLASS	Class 2: Gases
ADR PACK GROUP	#	ADR LABEL NO.	2.1
CEPIC TEC(R) NO.	20G5F	RID CLASS NO.	2.1
RID PACK GROUP	#	UN NO. SEA	1950
IMDG CLASS	2.1	IMDG PACK GR.	#
EMS	F-D, S-U	MFAG	See Guide
MARINE POLLUTANT	No.	UN NO. AIR	1950
AIR CLASS	2.1	AIR PACK GR.	#

15 REGULATORY INFORMATION

CONTAINS PETROLEUM DISTILLATE

RISK PHRASES

R10	Flammable.
R66	Repeated exposure may cause skin dryness or cracking.

WD40 AEROSOL**SAFETY PHRASES**

S2	Keep out of the reach of children
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S37	Wear suitable gloves.
S51	Use only in well-ventilated areas.
A1	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.

EU DIRECTIVES

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

STATUTORY INSTRUMENTS

Chemicals (Hazard Information and Packaging) Regulations.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION**REVISION COMMENTS**

Re-issued in accordance with Regulation (EC) No. 1907/2006 Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH).

REVISION DATE 09-2007

REV. NO./REPL. SDS GENERATED 3 / 02-2007

RISK PHRASES IN FULL

NC	Not classified.
R10	Flammable.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use. ,