


NSEV SERIES

85°C Bi-polar, Lead Free Reflow Soldering.

◆FEATURES

- Lead Free reflow soldering is available.
- Available for high density mounting.
- RoHS compliance.



◆SPECIFICATIONS


Items	Characteristics																					
Category Temperature Range	-40 ~+85°C																					
Rated Voltage Range	6.3~50V.DC																					
Capacitance Tolerance	± 20%(20°C,120Hz)																					
Leakage Current(MAX)	I=0.05CV or 10μA whichever is greater. (After 2 minutes application of rated voltage) I=Leakage Current(μA) C=Rated Capacitance(μF) V=Rated Voltage(V)																					
Dissipation Factor(MAX) (tanδ)	<table><tr><td>Rated Voltage (V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>tanδ</td><td>0.35</td><td>0.26</td><td>0.24</td><td>0.22</td><td>0.20</td><td>0.18</td></tr></table> (20°C,120Hz)	Rated Voltage (V)	6.3	10	16	25	35	50	tanδ	0.35	0.26	0.24	0.22	0.20	0.18							
Rated Voltage (V)	6.3	10	16	25	35	50																
tanδ	0.35	0.26	0.24	0.22	0.20	0.18																
Endurance	After applying rated voltage with rated ripple current for 2000hrs at 85°C, (The polarity shall be reversed every 500hrs.), the capacitors shall meet the following requirements. <table><tr><td>Capacitance Change</td><td>Within ±25% of the initial value.</td></tr><tr><td>Dissipation Factor</td><td>Not more than 200% of the specified value.</td></tr><tr><td>Leakage Current</td><td>Not more than the specified value.</td></tr></table>	Capacitance Change	Within ±25% of the initial value.	Dissipation Factor	Not more than 200% of the specified value.	Leakage Current	Not more than the specified value.															
Capacitance Change	Within ±25% of the initial value.																					
Dissipation Factor	Not more than 200% of the specified value.																					
Leakage Current	Not more than the specified value.																					
Low Temperature Stability Impedance Ratio(MAX)	<table><tr><td>Rated Voltage (V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Z(-25°C)/Z(20°C)</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-40°C)/Z(20°C)</td><td>8</td><td>8</td><td>4</td><td>4</td><td>3</td><td>3</td></tr></table> (120Hz)	Rated Voltage (V)	6.3	10	16	25	35	50	Z(-25°C)/Z(20°C)	4	3	2	2	2	2	Z(-40°C)/Z(20°C)	8	8	4	4	3	3
Rated Voltage (V)	6.3	10	16	25	35	50																
Z(-25°C)/Z(20°C)	4	3	2	2	2	2																
Z(-40°C)/Z(20°C)	8	8	4	4	3	3																

◆MULTIPLIER FOR RIPPLE CURRENT

Frequency coefficient

Frequency (Hz)	60(50)	120	500	1k	10k≤
Coefficient					
0.1~1μF	0.50	1.00	1.20	1.30	1.50
2.2~4.7μF	0.65	1.00	1.20	1.30	1.50
10~47μF	0.80	1.00	1.20	1.30	1.50


◆MARKING



◆PART NUMBER

 NSEV D×L
 Rated Voltage Series Rated Capacitance Capacitance Tolerance Option Case Size

(mm)

Size ϕ D×L(mm), Ripple Current (mA r.m.s./85°C, 120Hz)[illegible]