


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
C	RELEASE TO CN	7/11/07	D.FRISIELLO
D	REVISED MOLED BOOT	9/19/07	D.FRISIELLO




PART #	LENGTH
	FEET (METERS)
CC174-1	1.0 (.30)
CC174-1.5	1.5 (.46)
CC174-2	2.0 (.61)
CC174-2.5	2.5 (.76)
CC174-3	3.0 (.91)
CC174-4	4.0 (1.22)
CC174-5	5.0 (1.52)
CC174-7.5	7.5 (2.28)
CC174-10	10.0 (3.05)
CC174-12	12.0 (3.66)
CC174-15	15.0 (4.57)
CC174-25	25.0 (7.62)

NOTES:

1. CABLE SHALL BE TESTED FOR CONTINUITY.
2. CABLE SHALL BE ROHS COMPLIANT.
3. CABLE SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG.

DIMENSIONS ARE IN INCHES [mm]  
UNLESS OTHERWISE SPECIFIED,  
TOLERANCES TO BE:  
.X ±.1 [.25] ANGLES ±2°  
.XX ±.01 [.25]  
.XXX ±.005 [.13]  
OVERALL CABLE LENGTH TOL:  
≤ 60 [1524] +3 [76.2] / -0  
> 60 [1524] +5% / -0%



APPROVALS		DATE
DRAWN BY	C.MCCORMICK	05/03/2001
CHECKED BY	D.PARHAM	05/09/2001
APPROVED BY	R.CARRICK	05/14/2001

CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

<b>L-com</b> CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY		COAXIAL	
PRODUCT DESCRIPTION		CA BNC M /BNC M RG174/U	
SIZE	FSCM NO.	DWG. NO.	REV.
<b>A</b>	<b>43321</b>	<b>CC174</b>	<b>D</b>
SCALE: NONE		CAD FILE: CC174.SLDDRW	SHEET 1 OF 1