








11	10	89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	2-111492-6
	10	78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	2-111492-5
	10	70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	2-111492-4
	10	65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	2-111492-3
	10	57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	2-111492-2
	10	52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	2-111492-1
	10	47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	2-111492-0
	10	45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	1-111492-9
	10	39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	1-111492-8
	10	34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	1-111492-7
	10	32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	1-111492-6
	10	27.23 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	1-111492-5
11	10	95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	1-111492-4
11	2	95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	1-111492-3
11	2	89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	1-111492-2
DED	2	78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111492-1
	2	70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	1-111492-0
	2	65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	1-111492-9
	2	57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	111492-8
DED	2	52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	111492-7
DED	2	47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	111492-6
DED	2	45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	111492-5
11	2	39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	111492-4
11	2	34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	111492-3
DED	2	32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	111492-2
11	2	27.23 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	111492-1
	CONTACT FINISH	E	D	C	B	A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 8-9-90 C. OBERMAN CHK: 11-28-90 F. M. HEINEY		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± 1. PLC ± 2. PLC ± 0.1% .005 3. PLC ± 14. PLC ± ANGLES ± FINISH		NAME APVD: — PRODUCT SPEC 108-1336 APPLICATION SPEC 114-7011	
		WEIGHT —		SIZE A1	
MATERIAL MOLDED PARTS: 		CONTACTS: SEE TABLE		CAD CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-111492	
				RESTRICTED TO —	
				SCALE: 4:1 SHEET 1 of 1 REV J	