

GLASS PASSIVATED BRIDGE RECTIFIERS

REVERSE VOLTAGE - 50 to 1000 Volts
FORWARD CURRENT - 1.5 Amperes


FEATURES

- Rating to 1000V PRV
- Ideal for printed circuit board
- Low forward voltage drop, high current capability.
- Reliable low cost construction utilizing molded epoxy technique results in inexpensive product
- The plastic material has UL flammability classification 94V-0
- UL Recognition File # E95060

MECHANICAL DATA

- Case : Molded plastic
- Polarity: As marked on Body
- Weight : 0.05 ounces, 1.3 grams
- Mounting position : Any

WOG



WOG		
DIM.	MIN.	MAX.
A	8.84	9.86
B	25.4	-
C	27.9	-
D	4.00	4.60
E	0.71	0.81
F	4.60	5.60

All Dimensions in millimeter

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	W005G	W01G	W02G	W04G	W06G	W08G	W10G	UNIT
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @T _A =25°C	I _(AV)					1.5			A
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC METHOD)	I _{FSM}				50				A
Maximum forward Voltage at 1.0A DC	V _F			1.0					V
Maximum DC Reverse Current @T _J =25°C at Rated DC Blocking Voltage @T _J =125°C	I _R				5.0				uA
					500				uA
Typical Junction Capacitance per element (Note 1)	C _J			20					pF
Typical Thermal Resistance (Note 2)	R _{θJA}			36					°C/W
Operating Temperature Range	T _J			-55 to +150					°C
Storage Temperature Range	T _{STG}			-55 to +150					°C

NOTES : 1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

REV. 2, 01-Dec-2000, KBDD01

2. Thermal Resistance Junction to Ambient

RATING AND CHARACTERISTIC CURVES
W005G thru W10G

LITEON

FIG.1 - FORWARD CURRENT DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 - TYPICAL JUNCTION CAPACITANCE




FIG.4 - TYPICAL FORWARD CHARACTERISTICS




FIG.5 - TYPICAL REVERSE CHARACTERISTICS

