


9001 Series

DIN41612 Half B Type Male



Material:

Housing: 30% Glass Filled PBT UL94V-0.

Contacts: Copper Alloy.

Electrical Characteristics:

Current Rating: 2 A.

Dielectric Withstanding Voltage: AC 1000V.

Insulator Resistance: 1000M Ω min.

Contact Resistance: 20m Ω max.




Operating Temperature: -55°C ~+125°C.

Features:

* Mates with Female 2Row Half

9001-36 Half B Type.

9001-38 Half Q Type.



P.C. Board Layout

Dimension				
Position	A	B	C	D
32/16/8	54.00	46.26	47.40	44.60
20/10/5	38.04	33.02	31.80	29.40
Pitch	Position	Rows with Contacts	Contact Arrange	
2.54mm	32	a b		
	20	a b		
	16	a -		
	10	a -		
5.08mm	16	a b		
	10	a b		
	8	a -		
	5	a -		

Ordering information

9001-

Series

3

3: 2.54mm
4: 5.08mm

5

5: Male

32

Position

1

1: Dip Length

C

C: Dip Tin
Contact Gold
G: Gold

00

00: G/F
10: 10 μ "
15: 15 μ "
30: 30 μ "

L1

Blank: W/O
Lock
L1: With Lock

A

A: Tray
Package

See Page CA04

*Standard Gold Flash.