



(2,00 mm) .0787"

LTMM, ZLTMM SERIES

LTMM-110-02-F-D-RA

ZLTMM-112-75-L-D-285

LTMM-113-02-T-D

SHROUDED HEADER & STACKER

Mates with:
SQT, SQW, ESQT, SMM

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?LTMM or www.samtec.com?ZLTMM

Insulator Material:

High Temperature Nylon

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over

50µ" (1,27 µm) Ni

Current Rating:

3A per contact @ 80°C ambient

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max

ALSO AVAILABLE

Shrouded IDC headers and stackers to mate with TCSD Series. See STMM and ZSTMM Series.

Note: Other Gold plating options available. Contact Samtec.

Note: This Series is non-standard, non-returnable.

LTMM - **1** NO. PINS PER ROW - **02** - **PLATING OPTION** - **D** - **TAIL OPTION** - **OTHER OPTION**

04, 05, 06, 07, 08, 10, 12, 13, 15, 17, 20, 22, 25
(Call Samtec for other sizes)

-F
= Gold flash on post, Matte Tin on tail

-L
= 10µ" (0,25 µm) Gold on post, Matte Tin on tail

-T
= Matte Tin

Leave blank for Through-hole

-RA
= Right Angle

-SM
= Surface Mount

-“XX”
= Polarized Position

-LC
= Locking Clip (-SM only) (Manual placement required)

-K
= (7,50 mm) .295" DIA Film Pick & Place Pad (-SM only)

-TR
= Tape & Reel (-SM only)

ZLTMM - **1** NO. PINS PER ROW - **LEAD STYLE** - **PLATING OPTION** - **D** - **BODY HEIGHT** - **OTHER OPTION**

04, 05, 06, 07, 08, 10, 12, 13, 15, 17, 20, 22, 25
(Call Samtec for other sizes)

Specify LEAD STYLE from chart.

-F
= Gold flash on post, Matte Tin on tail

-L
= 10µ" (0,25 µm) Gold on post, Matte Tin on tail

-T
= Matte Tin

-“XXX”
= Body Height

-“XX”
= Polarized Position

LEAD STYLE	B (OAL)	MAX BODY HEIGHT
-75	(9,58) 0.377	(7,42) 0.292
-62	(10,08) 0.397	(7,92) 0.312
-65	(10,49) 0.413	(8,33) 0.328
-73	(12,09) 0.476	(9,93) 0.391
-63	(14,10) 0.555	(11,94) 0.470
-66	(15,09) 0.594	(12,93) 0.509
-69	(15,60) 0.614	(13,44) 0.529
-74	(17,09) 0.673	(14,94) 0.588
-70	(17,60) 0.693	(15,44) 0.608
-71	(21,08) 0.830	(18,92) 0.745
-72	(21,62) 0.851	(19,46) 0.766

Note: For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683