

Toggle Switches

Miniature - Sealed



Specifications:

Contact Rating	: 0.4 volt-amps (VA) maximum at 20V maximum (AC or DC).
Mechanical Life	: 30,000 make-and-break cycles.
Contact Resistance	: 10mΩ maximum initial at 2 to 4V dc. 100mA for both silver and gold plated contacts.
Minimum Insulation Resistance	: 1,000MΩ.
Dielectric Strength	: 1,000VRMS at sea level.
Operating Temperature	: -30°C to 85°C.


Materials:

Case and Bushing	: Glass filled nylon 66, heat stabilized.
Actuator	: Brass, chrome plated with internal, O-ring seal standard.
Switch Support	: Brass or steel, tin plated.
Switch Support Retainer	: Stainless steel.
Contacts/Terminals	: Copper alloy, with gold plated.

Pole Option


M2RE

SPDT



DPDT

Dimensions : Millimetres (Inches)



Dimensions : Millimetres (Inches)



Toggle Switches


Miniature - Sealed




Pole Option

M6RE


SPDT




PCB Mounting



DPDT




PCB Mounting




M7RE

SPDT



PCB Mounting



Toggle Switches

Miniature - Sealed




Pole Option

M7RE

DPDT

PCB Mounting



Soldering Process:

Manual soldering: Use soldering iron of 30 watts, controlled at 350°C approximately 5 seconds while applying solder.


Wave soldering:

Recommended soldering temperature : 260 ±5°C.

Duration of solder immersion: 5 ±1 seconds (PCB is 1.6mm in thickness).

Soldering: Vapour phase.

Temperature Profile		
Zone	Room Temperature (°C)	Time (seconds)
Pre-heat (A)	150°C	Minimum 120
Soak (B)	180°C to 200°C	Minimum 150
Peak (C)	200°C to 235°C	Minimum 30
Peak (D)	235°C to 260°C	Minimum 40
Peak (E)	260°C	Maximum 10



Toggle Switches

Miniature - Sealed



Specifications

Number of Poles	Switch Function			Connected Terminals/Schematic			Model Number
	Position 1	Position 2	Position 3	Position 1	Position 2	Position 3	
SP	On	None	Mom		N/A		1AS2
			On				1AS3
	Mom	Off	Mom		Open		1AS4
	On						1AS5
DP	On	None	On		N/A		1AD1
			Mom				1AD2
			On				1AD3
	Mom	Off	Mom		Open		1AD4
	On						1AD5
		On	On		2 - 3, 5 - 4		1AD6

Mom = Momentary

Specification Table

Description	Part Number
Switch, PCB, SPDT, Vertical, On-Mom	1AS2T2B4M2RE
Switch, PCB, SPDT, Vertical, Mom-Off-Mom	1AS4T2B4M2RE
Switch, PCB, SPDT, Vertical, On-Off-On	1AS3T2B4M2RE
Switch, PCB, SPDT, Vertical, On-Off-Mom	1AS5T2B4M2RE
Switch, PCB, DPDT, Vertical, On-Mom	1AD2T2B4M2RE
Switch, PCB, DPDT, Vertical, On-On	1AD1T2B4M2RE
Switch, PCB, DPDT, Vertical, Mom-Off-Mom	1AD4T2B4M2RE
Switch, PCB, DPDT, Vertical, On-Off-On	1AD3T2B4M2RE
Switch, PCB, DPDT, Vertical, On-Off-Mom	1AD5T2B4M2RE
Switch, PCB, DPDT, Vertical, On-On-On	1AD6T2B4M2RE
Switch, PCB, SPDT, Horizontal R/A, Mom-Off-Mom	1AS4T2B4M6RE
Switch, PCB, SPDT, Horizontal R/A, On-Off-Mom	1AS5T2B4M6RE
Switch, PCB, DPDT, Horizontal R/A, On-Mom	1AD2T2B4M6RE
Switch, PCB, DPDT, Horizontal R/A, On-On	1AD1T2B4M6RE
Switch, PCB, DPDT, Horizontal R/A, Mom-Off-Mom	1AD4T2B4M6RE
Switch, PCB, DPDT, Horizontal R/A, On-Off-On	1AD3T2B4M6RE
Switch, PCB, DPDT, Horizontal R/A, On-Off-Mom	1AD5T2B4M6RE



Toggle Switches


Miniature - Sealed



Specification Table

Description	Part Number
Switch, PCB, DPDT, Horizontal R/A, On-On-On	1AD6T2B4M6RE
Switch, PCB, SPDT, Vertical R/A, On-Mom	1AS2T2B4M7RE
Switch, PCB, SPDT, Vertical R/A, Mom-Off-Mom	1AS4T2B4M7RE
Switch, PCB, SPDT, Vertical R/A, On-Off-On	1AS3T2B4M7RE
Switch, PCB, SPDT, Vertical R/A, On-Off-Mom	1AS5T2B4M7RE
Switch, PCB, DPDT, Vertical R/A, On-Mom	1AD2T2B4M7RE
Switch, PCB, DPDT, Vertical R/A, On-On	1AD1T2B4M7RE
Switch, PCB, DPDT, Vertical R/A, Mom-Off-Mom	1AD4T2B4M7RE
Switch, PCB, DPDT, Vertical R/A, On-Off-On	1AD3T2B4M7RE
Switch, PCB, DPDT, Vertical R/A, On-Off-Mom	1AD5T2B4M7RE
Switch, PCB, DPDT, Vertical R/A, On-On-On	1AD6T2B4M7RE

Part Number Explanation:



Model Number	: 1AS2 = SP On-None-Mom, 1AS3 = SP On-Off-On, 1AS4 = SP Mom-Off-Mom, 1AS5 = SP On-Off-Mom, 1AD1 = DP On-None-On, 1AD2 = DP On-None-Mom, 1AD3 = DP On-Off-On, 1AD4 = DP Mom-Off-Mom, 1AD5 = DP On-Off-Mom and 1AD6 = DP On-On-On.
Actuator	: T2 = 7.62 High.
Bushing	: B4 = 6.10 High.
Terminations	: M2 = PVC Through Hole, M6 = Right Angle, PVC Through Hole and M7 = Vertical Right Angle, PVC Through Hole.
Contact Material	: R = Gold.
Seal	: E = Epoxy (STD).

Toggle Switches

Miniature - Sealed



Notes:

International Sales Offices:



AUSTRALIA - Farnell

Tel No: ++61 1300 361 005
Fax No: ++61 1300 361 225



FINLAND - Farnell

Tel No: ++358 9 560 7780
Fax No: ++358 9 345 5411



ITALY - Farnell

Tel No: ++39 02 93 995 200
Fax No: ++39 02 93 995 300



SPAIN - Farnell

Tel No: 901 20 20 80
Fax No: 901 20 20 90



AUSTRIA - Farnell

Tel No: ++43 662 2180 680
Fax No: ++43 662 2180 670



FRANCE - Farnell

Tel No: ++33 474 68 99 99
Fax No: ++33 474 68 99 90



MALAYSIA - Farnell-Newark

Tel No: ++60 3 7873 8000
Fax No: ++60 3 7873 7000



SWEDEN - Farnell

Tel No: ++46 8 730 50 00
Fax No: ++46 8 83 52 62



BELGIUM - Farnell

Tel No: ++32 3 475 2810
Fax No: ++32 3 227 3648



GERMANY - Farnell

Tel No: ++49 89 61 39 39 39
Fax No: ++49 89 613 59 01



NETHERLANDS - Farnell

Tel No: ++31 30 241 7373
Fax No: ++31 30 241 7333



SWITZERLAND - Farnell

Tel No: ++44 204 64 64
Fax No: ++44 204 64 54



BRAZIL - Farnell-Newark

Tel No: ++55 11 4066 9400
Fax No: ++55 11 4066 9410



HONG KONG - Farnell-Newark

Tel No: ++852 2268 9888
Fax No: ++852 2268 9899



NEW ZEALAND - Farnell

Tel No: 0800 90 80 80
Fax No: 0800 90 80 81



UK - Farnell

Tel No: ++44 8701 200 200
Fax No: ++44 8701 200 201



CHINA - Farnell-Newark

Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



HUNGARY - Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



NORWAY - Farnell

Tel No: 800 146 70
Fax No: 800 146 76



UK - CPC

++44 8701 202 530
++44 8701 202 531



CZECH REPUBLIC - Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



INDIA - Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



PORTUGAL - Farnell

Tel No: ++34 93 475 8804
Fax No: ++34 93 474 5288



USA - Newark

Tel No: 800 463 9275



DENMARK - Farnell

Tel No: ++45 44 53 66 44
Fax No: ++45 44 53 66 06



IRELAND - Farnell

Tel No: ++353 1 830 9277
Fax No: ++353 1 830 9016



RUSSIA - Farnell

Tel No: ++44 870 1200 208
Fax No: ++44 870 1200 209



SINGAPORE - Farnell-Newark

Tel No: ++65 6788 0200
Fax No: ++65 6788 0300



ESTONIA - Farnell

Tel No: ++358 9 560 7780
Fax No: ++358 9 345 5411



ISRAEL - Farnell

Tel No: ++180 937 0015
Fax No: ++180 937 0014



EXPORT - Farnell

Tel No: ++44 8701 200 208
Fax No: ++44 8701 200 209

For enquiries from all other markets

<http://www.farnell.com>
<http://www.newark.com>
<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.

