

**SERIES:** CSXX12B | **DESCRIPTION:** CURRENT SENSOR**FEATURES**

- open loop
- bipolar
- detects current direction
- single channel

**MODEL**

	rated current [I_f]	linearity range ¹ [I_m]
	[A_{RMS}]	[A_{PEAK}]
CS0312B	±3	+9/-3
CS0512B	±5	+15/-5
CS1012B	±10	+30/-10
CS1512B	±15	+45/-15
CS2012B	±20	+60/-20

Notes: 1. I_m is the maximum peak current for which the output voltage specifications are guaranteed, however the I_f RMS rating must not be exceeded.
2. All specifications measured at 25°C, $R_L=10\text{ k}\Omega$, unless otherwise noted.
3. It is recommended to add a 1 μF capacitor connected between the common terminal 4 and the +12 V terminal 1 to avoid noise problems.

SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
supply voltage [V_{CC}]		11.4	12.0	12.6	V
max current consumption [I_C]				25	mA
output voltage [V_O]	at $+I_f$	4.47	4.50	4.53	V
	at $-I_f$	0.47	0.50	0.53	V
zero current offset voltage [V_r]	after demagnetization	2.48	2.50	2.52	V
output voltage linearity ⁴ [ΔK_o]				±0.5	%
response [t_r]	at $di/dt = I_f/\mu\text{s}$		3		μs
output voltage temperature characteristics				±0.1	%/°C
zero current offset voltage characteristics				±1.5	mV/°C
hysteresis [V_h]	at $+I_f$ to zero current			8	mV
primary over current	for maximum 50 ms, no damage			10* I_f	A
withstand voltage	between coil and each terminal for 1 minute		2,000		Vac
insulation resistance	between coil and each terminal at 500 Vdc		500		M Ω
operating temperature		-10		75	°C
storage temperature		-30		90	°C
safety approvals	UL 508				
flammability rating	UL94V-0				
RoHS	yes				

Notes: 4. Deducting the value of hysteresis and offset voltage, calculated by $(V/V_O)/(|I_f|-1)\times 100\%$.

SOLDERABILITY

parameter	conditions/description	min	typ	max	units
hand soldering	for maximum 3 seconds		280		°C

MECHANICAL


parameter	conditions/description	min	typ	max	units
dimensions	15 x 15 x 20				mm
case material	PBT				
terminals	phosphor bronze with tin plating				
weight			8		g

MECHANICAL DRAWING

units: mm
tolerance: ±0.5 mm

PIN CONNECTIONS	
PIN	FUNCTION
1	+12 V
2	NC
3	Output (V)
4	0 V
5	+Input (A)
6	-Input (A)

MODEL NO.	ØA [mm]	ØB [mm]
CS0312B	0.6	1.2
CS0512B	0.9	1.5
CS1012B	1.1	1.7
CS1512B	1.4	2.0
CS2012B	1.7	2.3




DERATING CURVE






PERFORMANCE CURVES

Output Voltage vs. Input Current



Input Current Frequency vs. Output Attenuation

Output Voltage vs. Ambient Temperature
(at $+I_f$)Offset Voltage vs. Ambient Temperature
(at Zero Current)

REVISION HISTORY

rev.	description	date
1.0	initial release	09/03/2019
1.01	brand update	02/21/2020
1.02	logo, datasheet style update	08/05/2022
1.03	CUI Devices rebranded to Same Sky	09/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com