








▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	ON
2-3; 5-6	N/A	2-1; 5-4




NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- STATIONARY CONTACTS: COPPER ALLOY W/GOLD PLATING
- MOVING CONTACTS: COPPER ALLOY W/ GOLD PLATING
- RATING: 0.4 VA max. @ 20V AC OR DC max.
- CONTACT RESISTANCE: <100 MILLI-OHM
- MECHANICAL LIFE: 40,000 MAKE-AND-BREAK CYCLES.
- INSULATION RESISTANCE: 500 MEGA-OHM min.
- DIELECTRIC STRENGTH: 500 V RMS @SEA LEVEL.
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- SEAL RATING: IP67
- 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC



B	19606	UPDATE PLATING NOTE	01/20/11	BMA
A	19141	New Release	6/15/10	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 200UDP1T1A1M6RE

SCALE 2:1

DATE 2/12/2010

DR RC

DWG T250004

REV B