

NOTES:

1. MATERIALS AND FINISHES(PLATING THICKNESS IN MICRO-INCHES):

BODY – BRASS, ALBALOY PLATING

CONTACT – BERYLLIUM COPPER, GOLD PLATING

INSULATOR – PTFE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. FREQUENCY RANGE: DC 0–6 GHz

C. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.

3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.

B. TEMPERATURE RANGE: –55°C to +165°C

THIRD ANGLE PROJ.



REV

DESCRIPTION

DATE

ECO

APPR

B

1.9±0.25 WAS 1.9±0.05

07–Oct–05

ROCKY

C

SEE SHEET 1

10–Nov–06

JEKY

D

SEE SHEET 1

31–Dec–07


KATE

E

SEE SHEET 1

31–Aug–09

SCOTT.H



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 – 6mm 6 – 30mm 30 – 120mm ANGLES ±0.1mm ±0.2mm ± 0.3mm ±1°	MATERIAL	DRAWN	DATE	TITLE QMA(F) STR BULKHEAD RCPT FRONT MOUNT			Amphenol RF	
		ENGINEER	DATE				Danbury CT USA, Tainan Taiwan, Shenzhen China	
		APPROVED	DATE				www.amphenolrf.com	
		CAD FILE						
NOTICE – These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	SCOTT.H	21–Aug–09	SCALE: 6/1			DRAWING NO.	930–127J–51S
				SHEET 2 OF 2			ITEM NO.	930–127J–51S
				DWG SIZE	CODE ID	REV	PART NO.	930–127J–51S
		FINISH	F:\DWG\CNPD\930\127J\51S–ESZ	B	74868	E		