

**General ordering data**

Order No.	1028700000
Part designation	WFF 300
Version	Stud terminal, 300 mm ² , Threaded stud connection, Wemid, dark beige, TS 35
EAN	4008190165017
Qty.	4 pc(s).

Product notes

Note, accessories	WAH 185/300 in blue, order no. 1064780000
-------------------	---

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA98ATEX1684U
Download, German	KEMA98ATEX1684U_d.pdf
Download English	KEMA98ATEX1684U_e.pdf
ATEX voltage	1100 V
ATEX current	452 A
ATEX conductor cross-section	300 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	dark beige
Connection direction	on side
End plate required	No
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1

Additional technical data

No. of terminal strips per level	2
Open sides	closed
Operating temperature range	- 50 °C, + 120 °C
Product family	W-Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	510 A
Min. cross-section (CSA)	AWG 6
Max. cross-section (CSA)	kcmil 600

Conductors for clamping (rated connection)

Type of connection	Threaded stud connection
Connection direction	on side
Flexible, min.	25 mm ²
Flexible, max.	240 mm ²

Dimensions

Width	55 mm
Height of lowest version	86 mm
Length	163 mm
Weight	552.15 g
TS 35 offset	81.5 mm

Rating data

Rated cross-section	300 mm ²
Rated voltage	1,000 V
Rated impulse voltage	8 kV
Rated current	520 A
Current with max. conductor	520 A
Pollution severity	3

Strap connection

Strap 1, max.	3 x 35 x 1
Strap 1, min.	2 x 4 x 1
Strap 2, max.	8 x 32 x 1
Strap 2, min.	6 x 32 x 1

Stud connection

2 cable lugs to DIN 46234	50...240 mm ²
2 cable lugs to DIN 46234	25...240 mm ²
Cable lug to DIN 46234	50...300 mm ²
Cable lug to DIN 46234	25...240 mm ²
Clamping range, max.	300 mm ²
Clamping range, min.	25 mm ²
Stud size for spade connection	M 16
Tightening torque range	25...60 Nm

Stud connection**UL rating data**

Voltage (UL)	1,000 V
Current (UL)	500 A
Min. cross-section (UL)	AWG 6
Max. cross-section (UL)	kcmil 600

Approvals

Approvals institutes

**Downloads**

STEP	1028700000_17248_WFF_300_STP.stp
------	----------------------------------

Classifications

eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK

Similar products

Order No.	Part designation	Version
1028300000	WFF 35	Stud terminal, 35 mm ² , Threaded stud connection, Wemid, dark beige, TS 35
1028380000	WFF 35 BL	Stud terminal, 35 mm ² , Threaded stud connection, Wemid, blue, TS 35
1028400000	WFF 70	Stud terminal, 70 mm ² , Threaded stud connection, Wemid, dark beige, TS 35
1028480000	WFF 70 BL	Stud terminal, 70 mm ² , Threaded stud connection, Wemid, blue/light blue, TS 35
1028500000	WFF 120	Stud terminal, 120 mm ² , Threaded stud connection, Wemid, dark beige, TS 35
1028580000	WFF 120 BL	Stud terminal, 120 mm ² , Threaded stud connection, Wemid, blue, TS 35
1857540000	WFF 120/M12/AH	Stud terminal, 120 mm ² , Screw connection, Wemid, dark beige, TS 35
1028600000	WFF 185	Stud terminal, 185 mm ² , Threaded stud connection, Wemid, dark beige, TS 35



1028680000 WFF 185 BL

Stud terminal, 185 mm², Threaded stud connection, Wemid, blue,
TS 35