



Looking for more information?

Visit us on the web at <http://www.artisan-scientific.com> for more information:

- Price Quotations
- Drivers
- Technical Specifications, Manuals and Documentation

Artisan Scientific is Your Source for Quality New and Certified-Used/Pre-owned Equipment

- Tens of Thousands of In-Stock Items
- Hundreds of Manufacturers Supported
- Fast Shipping and Delivery
- Leasing / Monthly Rentals
- Equipment Demos
- Consignment

Service Center Repairs

Experienced Engineers and Technicians on staff in our State-of-the-art Full-Service In-House Service Center Facility

InstaView™ Remote Inspection

Remotely inspect equipment before purchasing with our Innovative InstaView™ website at <http://www.instraview.com>

We buy used equipment! We also offer credit for Buy-Backs and Trade-Ins

Sell your excess, underutilized, and idle used equipment. Contact one of our Customer Service Representatives today!

Talk to a live person: 888-88-SOURCE (888-887-6872) | Contact us by email: sales@artisan-scientific.com | Visit our website: <http://www.artisan-scientific.com>

Function Generator

B1



GFG-8216A (3MHz)

GFG-8215A (3MHz)

FEATURES

- * Frequency Range: 0.3Hz ~ 3MHz
- * Waveforms: Sine, Triangle, Square, Ramp, TTL and CMOS Output
- * External Voltage Controlled Frequency (VCF) Function
- * Duty Cycle Control with Signal Inversion Capability

- * Variable DC Offset Control
- * Two-Step (-20dBx2) and Variable Attenuator
- * Built-In 6 Digit Counter with INT/EXT Function Up to 150MHz / High Resolution(GFG-8216A)

SPECIFICATIONS

MAIN	
Frequency Range	0.3Hz ~ 3MHz (7 Range)
Amplitude	> 10Vpp (into 50Ω load)
Impedance	50Ω ±10%
Attenuator	-20dB ± 1dBx2
DC Offset	<-5V ~ >5V (into 50Ω load)
Duty Control	80% : 20% : 80% to 1MHz Continue variable
Display	6 digit LED display
Range Accuracy	*GFG-8215A does not have display. ± 5%+1Hz (at 3 position) for GFG-8215A
SINE WAVE	
Distortion	≤ 1%, 0.3Hz ~ 200kHz
Flatness	< 0.3dB, 0.3Hz ~ 300kHz < 0.5dB, 300kHz ~ 3MHz
TRIANGLE WAVE	
Linear	≥ 98%, 0.3Hz ~ 100kHz ≥ 95%, 100kHz ~ 3MHz
SQUARE WAVE	
Symmetry	± 2%, 0.3Hz ~ 100kHz
Rise or Fall Time	≤ 100nS at maximum output (into 50Ω load)
CMOS OUTPUT	
Level	4Vpp±1Vpp ~ 14.5Vpp±0.5Vpp adjustable
Rise or Fall Time	≤ 120nS
TTL OUTPUT	
Level	≥ 3Vpp
Fan Out	20 TTL load
Rise or Fall Time	≤ 25nS
VCF	
Input Voltage	0V ~ 10V ±1V (100 : 1)
Input Impedance	10kΩ ±10%
FREQUENCY COUNTER(For GFG-8216A Only)	
INT./EXT.	Switch selector
Range	0.3Hz ~ 3MHz (5Hz ~ 150MHz EXT.)
Accuracy	Time base accuracy ± 1 count
Time Base	± 20ppm(23° C±5 °C)after 30 minutes warm up
Resolution	The maximum resolution is 100nHz for 1Hz and 1Hz for 100MHz
Input Impedance	1MΩ // 150pF
Sensitivity	≤ 35mVrms (5Hz ~ 100MHz) ≤ 45mVrms (100MHz ~ 150MHz)

POWER SOURCE

AC115V/230V ± 15%, 50/60Hz

ACCESSORIES

Instruction manual x 1, Power cord x 1, GTL-101 x 2;
GTL-101x1 for GFG-8215A

DIMENSIONS & WEIGHT

251(W) x 91(H) x 291(D)mm, Approx. 2.1kg

ORDERING INFORMATION

GFG-8216A	3MHz Function Generator with 6Digit LED Display
GFG-8215A	3MHz Function Generator



Looking for more information?

Visit us on the web at <http://www.artisan-scientific.com> for more information:

- Price Quotations
- Drivers
- Technical Specifications, Manuals and Documentation

Artisan Scientific is Your Source for Quality New and Certified-Used/Pre-owned Equipment

- Tens of Thousands of In-Stock Items
- Hundreds of Manufacturers Supported
- Fast Shipping and Delivery
- Leasing / Monthly Rentals
- Equipment Demos
- Consignment

Service Center Repairs

Experienced Engineers and Technicians on staff in our State-of-the-art Full-Service In-House Service Center Facility

InstaView™ Remote Inspection

Remotely inspect equipment before purchasing with our Innovative InstaView™ website at <http://www.instraview.com>

We buy used equipment! We also offer credit for Buy-Backs and Trade-Ins

Sell your excess, underutilized, and idle used equipment. Contact one of our Customer Service Representatives today!

Talk to a live person: 888-88-SOURCE (888-887-6872) | Contact us by email: sales@artisan-scientific.com | Visit our website: <http://www.artisan-scientific.com>