

SI-3000C Series

5-Terminal, Full-Mold, Low Dropout Voltage Linear Regulator ICs

Features

- Compact full-mold package (equivalent to TO220)
- Output current: 1.5A
- Low dropout voltage: $V_{DIF} \leq 1V$ (at $I_o=1.5A$)
- Variable output voltage (rise only)
Available for remote sensing
- Output ON/OFF control terminal is compatible with LS-TTL.
(It can be driven directly by LS-TTL or standard CMOS logic.)
- Built-in foldback overcurrent (SI-3033C: Drooping type overcurrent), input-overvoltage and thermal protection circuits

Absolute Maximum Ratings

($T_a=25^{\circ}C$)

Parameter	Symbol	Ratings				Unit
		SI-3033C	SI-3050C/3090C	SI-3120C/3150C	SI-3240C	
DC Input Voltage	V_{IN}	20	35	35	45	V
Output Control Terminal Voltage	V_c	V_{IN}				V
DC Output Current	I_o	1.5^{*2}				A
Power Dissipation	P_{D1}	18(With infinite heatsink)				W
	P_{D2}	1.5(Without heatsink, stand-alone operation)				W
Junction Temperature	T_j	-40 to $+125$				$^{\circ}C$
Operating Ambient Temperature	T_{op}	-30 to $+100$				$^{\circ}C$
Storage Temperature	T_{stg}	-40 to $+125$				$^{\circ}C$
Thermal Resistance (junction to case)	θ_{j-c}	5.5				$^{\circ}C/W$
Thermal Resistance (junction to ambient air)	θ_{j-a}	66.7(Without heatsink, stand-alone operation)				$^{\circ}C/W$

Applications

- For stabilization of the secondary-side output voltage of switching power supplies
- Electronic equipment

Electrical Characteristics

($T_a=25^{\circ}C$ unless otherwise specified)

Parameter		Symbol	Ratings									Unit
			SI-3033C			SI-3050C			SI-3090C			
			min.	typ.	max.	min.	typ.	max.	min.	typ.	max.	
Input Voltage		V _{IN}	3		15 ²	6 ³		30 ²	10 ³		30 ²	V
Output Voltage	SI-3000C ^{*1}	V _O	3.168	3.300	3.432	4.80	5.00	5.20	8.64	9.00	9.36	V
	SI-3000CA		3.234	3.300	3.366	4.90	5.00	5.10	8.82	9.00	9.18	
		Conditions	V _{IN} =5V, I _O =1.0A			V _{IN} =8V, I _O =1.0A			V _{IN} =12V, I _O =1.0A			
Dropout Voltage		V _{DIF}			0.5			0.5			0.5	V
		Conditions	I _O ≤1.0A									
					1.0			1.0			1.0	
		Conditions	I _O ≤1.5A									
Line Regulation		ΔV _{OLINE}		10	30		10	30		18	48	mV
		Conditions	V _{IN} =4.5 to 12V, I _O =1.0A			V _{IN} =6 to 15V, I _O =1.0A			V _{IN} =10 to 20V, I _O =1.0A			
Load Regulation		ΔV _{OLOAD}		40	100		40	100		70	180	mV
		Conditions	V _{IN} =5V, I _O =0 to 1.5A			V _{IN} =8V, I _O =0 to 1.5A			V _{IN} =12V, I _O =0 to 1.5A			
Temperature Coefficient of Output Voltage		ΔV _O /ΔT _a		±0.5			±0.5			±1.0		mV/°C
		Conditions	V _{IN} =5V, I _O =5mA, T _J =0 to 100°C			V _{IN} =8V, I _O =5mA, T _J =0 to 100°C			V _{IN} =12V, I _O =5mA, T _J =0 to 100°C			
Ripple Rejection		R _{REJ}		54			54			54		dB
		Conditions	V _{IN} =5V, f=100 to 120Hz			V _{IN} =8V, f=100 to 120Hz			V _{IN} =12V, f=100 to 120Hz			
Quiescent Circuit Current		I _q		3	10		5	10		5	10	mA
		Conditions	V _{IN} =5V, I _O =0A			V _{IN} =8V, I _O =0A			V _{IN} =12V, I _O =0A			
Overcurrent Protection Starting Current ^{*4,6}		I _{S1}	1.6			1.6			1.6			A
		Conditions	V _{IN} =5V			V _{IN} =8V			V _{IN} =12V			
V _C Terminal ^{*5}	Control Voltage (Output ON)	V _C . I _H	2.0			2.0			2.0			V
	Control Voltage (Output OFF)	V _C . I _L			0.8			0.8			0.8	
	Control Current (Output ON)	I _C . I _H			20			20			20	μA
		Conditions	V _C =2.7V									
	Control Current (Output OFF)	I _C . I _L			−0.3			−0.3			−0.3	mA
		Conditions	V _C =0.4V									

*1: In some cases, "A" may be printed on the right of the marking.
*2: $V_{IN(max)}$ and $I_o(max)$ are restricted by the relation $P_{D(max)}=(V_{IN}-V_o) \cdot I_o=18(W)$.
*3: Refer to the Dropout Voltage parameter. (Refer to Setting DC Input Voltage on page 9.)
*4: I_{s1} is specified at the 5% drop point of output voltage V_o on the condition that $V_{IN}=V_o+3V, I_o=1A$.
*5: Output is ON even when output control terminal V_c is open. Each input level is equivalent to LS-TTL level. Therefore, the device can be driven directly by LS-TTLs.
*6: These products (except for SI-3033C) cannot be used in the following applications because the built-in foldback-type overcurrent protection may cause errors during start-up stage.
(1) Constant current load (2) Positive and negative power supply (3) Series-connected power supply (4) V_o adjustment by raising ground voltage

Electrical Characteristics

(Ta=25°C unless otherwise specified)

Parameter		Symbol	Ratings									Unit
			SI-3120C			SI-3150C			SI-3240C			
			min.	typ.	max.	min.	typ.	max.	min.	typ.	max.	
Input Voltage		V _{IN}	13 ⁻³		30 ⁻²	16 ⁻³		30 ⁻²	25 ⁻³		40 ⁻²	V
Output Voltage	SI-3000C *1	V _O	11.52	12.00	12.48	14.40	15.00	15.60	23.04	24.00	24.96	V
	SI-3000CA		11.76	12.00	12.24	14.70	15.00	15.30	23.52	24.00	24.48	
Dropout Voltage		Conditions	V _{IN} =15V, I _O =1.0A			V _{IN} =18V, I _O =1.0A			V _{IN} =27V, I _O =1.0A			V
		V _{DIF}			0.5			0.5			0.5	
		Conditions	I _O ≤1.0A									
					1.0			1.0			1.0	
		Conditions	I _O ≤1.5A									
Line Regulation		ΔV _{OLINE}		24	64		30	90		48	128	mV
		Conditions	V _{IN} =13 to 25V, I _O =1.0A			V _{IN} =16 to 25V, I _O =1.0A			V _{IN} =25 to 38V, I _O =1.0A			
Load Regulation		ΔV _{OLOAD}		93	240		120	300		120	300	mV
		Conditions	V _{IN} =15V, I _O =0 to 1.5A			V _{IN} =18V, I _O =0 to 1.5A			V _{IN} =27V, I _O =0 to 1.5A			
Temperature Coefficient of Output Voltage		ΔV _O /ΔT _a		±1.5			±1.5			±2.5		mV/°C
		Conditions	V _{IN} =15V, I _O =5mA, T _J =0 to 100°C			V _{IN} =18V, I _O =5mA, T _J =0 to 100°C			V _{IN} =27V, I _O =5mA, T _J =0 to 100°C			
Ripple Rejection		R _{REJ}		54			54			54		dB
		Conditions	V _{IN} =15V, f=100 to 120Hz			V _{IN} =18V, f=100 to 120Hz			V _{IN} =27V, f=100 to 120Hz			
Quiescent Circuit Current		I _q		5	10		5	10		5	10	mA
		Conditions	V _{IN} =15V, I _O =0A			V _{IN} =18V, I _O =0A			V _{IN} =27V, I _O =0A			
Overcurrent Protection Starting Current*4,6		I _{S1}	1.6			1.6			1.6			A
		Conditions	V _{IN} =15V			V _{IN} =18V			V _{IN} =27V			
V _C Terminal*5	Control Voltage (Output ON)	V _C IH	2.0			2.0			2.0			V
	Control Voltage (Output OFF)	V _C IL			0.8			0.8			0.8	V
	Control Current (Output ON)	I _C IH			20			20			20	μA
	Conditions	V _C =2.7V										
	Control Current (Output OFF)	I _C IL			-0.3			-0.3			-0.3	mA
		Conditions	V _C =0.4V									

*1: In some cases, "A" may be printed on the right of the marking.

*2: V_{IN(max)} and I_{O(max)} are restricted by the relation P_{D(max)}=(V_{IN}-V_O)•I_O=18(W).

*3: Refer to the Dropout Voltage parameter. (Refer to Setting DC Input Voltage on page 9.)


*4: I_{S1} is specified at the 5% drop point of output voltage V_O on the condition that V_{IN}=V_O+3V, I_O=1A.*5: Output is ON even when output control terminal V_C is open. Each input level is equivalent to LS-TTL level. Therefore, the device can be driven directly by LS-TTLs.

*6: These products cannot be used in the following applications because the built-in foldback-type overcurrent protection may cause errors during start-up stage.

(1) Constant current load (2) Positive and negative power supply (3) Series-connected power supply (4) V_O adjustment by raising ground voltage

External Dimensions (TO220F-5)

(unit : mm)




- a. Part Number
- b. Lot Number


- Pin Assignment
- ① GND
 - ② V_c
 - ③ V_o
 - ④ V_{os}
 - ⑤ V_{IN}

Plastic Mold Package Type
Flammability: UL94V-0
Product Mass: Approx. 2.3g

Block Diagram



Typical Connection Diagram



C_0 : Output capacitor (47 to 100 μ F)

*1 C_1 } : Oscillation prevention capacitors


C_2 } (Approx. C_1 : 47 μ F, C_2 : 0.33 μ F)

These capacitors are required if the input line contains inductance or the wiring is long. Especially at low temperatures, tantalum capacitors are recommended for C_1 and C_0 .

*2 D_1 : Protection diode


This diode is required for protection against reverse biasing of the input and output. Sanken EU2Z is recommended.

T_a - P_D Characteristics



External Variable Output Voltage Circuit

1. Variable output voltage with a single external resistor




The output voltage may be increased by inserting resistor R_{EX} between terminals No.4 (sensing terminal) and No.3 (output terminal). The current I_{REX} flowing into terminal No.4 is 1mA (typ.)(SI-3033C:0.43mA (typ.)), therefore the adjusted output voltage V_{OUT} is:


$$V_O = V_{04} + I_{REX} \cdot R_{EX} \quad *V_{04}: \text{output voltage of SI-3000C series}$$

However, the internal resistor (between terminals No. 4 and No.1) is a semiconductor resistor, which has approximately thermal characteristics of +0.2%/°C.

It is important to keep the thermal characteristics in mind when adjusting the output voltage.



2. Variable output voltage with two external resistors



The output voltage may be increased by inserting resistors R_{EX1} between terminals No.4 (sensing terminal) and No.3 (output terminal) and R_{EX2} between terminals No.4 and No.1 (ground terminal).

The current I_{4IN} flowing into terminal No.4 is 1mA (typ.)(SI-3033C: 0.43mA (typ.)) so the thermal characteristics may be improved compared to the method shown in 1 by setting the external current I_{REX1} at approximately 5 times the value of I_{4IN} (stability coefficient $S=5$).

The adjusted output voltage V_{OUT} in this case is:


$$\begin{cases} V_O = V_{04} + R_{EX1} \cdot I_{REX1} \\ I_{REX1} = S \cdot I_{4IN} \end{cases}$$

The value of the external resistors may be obtained as follows:

$$R_{EX1} = \frac{V_O - V_{04}}{S \cdot I_{4IN}}, \quad R_{EX2} = \frac{V_{04}}{(S-1) \cdot I_{4IN}}$$

* V_{04} : Output voltage of SI-3000C series

S: Stability coefficient of I_{4IN} (may be set to any value)




Note: In the SI-3000C series, the output voltage increase can be adjusted as mentioned above. However, when the rise is set to approximately 10V compared to output voltage V_{04} , the necessary output current may not be obtained due to the S.O.A. protection circuit in the SI-3000C series.


■Typical Characteristics

($T_a=25^\circ\text{C}$)


I_o vs. V_{DIF} Characteristics




Temperature Coefficient of Output Voltage(SI-3050C)




Circuit Current(SI-3050C)




Output Voltage(SI-3033C)




Output Voltage(SI-3050C)




Output Voltage(SI-3240C)




Overcurrent Protection Characteristics(SI-3033C)




Overcurrent Protection Characteristics(SI-3050C)




Overcurrent Protection Characteristics(SI-3240C)



ON/OFF Control Characteristics(SI-3050C)



Thermal Protection Characteristics(SI-3050C)



Note on Thermal Protection:

The thermal protection circuit is intended for protection against heat during instantaneous short-circuiting. Its operation is not guaranteed for continuous heating condition such as short-circuiting over extended periods of time.