





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		P3	REVISED PER ECO-15-016062	10NOV15	KG	CD



1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
 3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
 4. PACKAGE STAMPED M24308/2-281F
 5. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M39029/63-368 OR ANY AMP HD-20 SOCKET CONTACT
- △6 AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- △7 UL/CSA DESIGNATION STAMPED IN THIS AREA.
- △8 RESTRICTED ITAR DRAWING.
- △9 FINISH: PLATED BRIGHT TIN .000400 MIN THK PER ASTM-B-545 OVER COPPER PLATE .000050 MIN THK PER MIL-C-14550.



SUPSC BY 205161-1	△9	STEEL, CLASS G	205161-5
	-	-	205161-4
	CADMIUM PER QQ-P-416	STEEL, CLASS G	205161-3
	CADMIUM PER QQ-P-416	BRASS	205161-2
SUPSD BY 207253-2	CADMIUM PER QQ-P-416	STEEL, CLASS G	205161-1
SHELL FINISH		SHELL MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 1-12-05	 TE Connectivity						
DIMENSIONS: INCHES		CHK D.MILLER 1-12-05							
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.MILLER 1-12-05	NAME RCPT ASSY,AMPLIMITE, SIZE 1,9 POSN,SERIES 109 —					
	0 PLC ± —		PRODUCT SPEC —						
	1 PLC ± —		—						
	2 PLC ± —		APPLICATION SPEC —						
	3 PLC ± .005		—						
4 PLC ± —		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH	WEIGHT		A2 00779 C-205161		—		
SEE CALLOUTS		SEE CALLOUTS	CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1	REV P3