

- Designed to comply with the requirements of GR1089, UL1950, EN60950, BABT and CSA950 to provide a supplementary insulation barrier with a working voltage of 250V
- UL File Number E150991
- Minimum interwinding breakdown voltage of 1500 Vrms
- Operating and storage temperature range: -40° to +85° C
- Meets IEC 695, 2-2 flammability requirements
- PWB Process Capability: standard printed wiring board assembly techniques, total-immersion cleaning
- Reliability testing: shock, vibration, temperature cycling, temperature - humidity - bias

ELECTRICAL SPECIFICATIONS AT 25° C


Part Number	Turns Ratio ±2%	Inductance ¹ μH ±10%	Leakage Inductance ³ μH max	DCR Ω max		Harmonic Distortion ² dB max
	Chip : Line	Line Side	Line Side	Chip Side	Line Side	30 kHz +10 dBm on 100 Ω load on Line Side
S560-6611-19	1 : 1	500	4	4.4	4.4	75

All measurements are made with pins 2 and 3 connected and pins 6 and 7 connected

- Inductance measured at 10 kHz, 0.1 Vac load on line side
- Measurements made with 100Ω source and 100Ω load impedance
- Leakage inductance measured at 100 kHz, 0.1 Vac


SCHEMATIC

S560-6611-19




MECHANICAL


S560-6611-19



Suggested PCB Pad Layout



Dimensions are in inches [millimeters].
 Standard dimension tolerance is ± 0.005 [0.13] unless otherwise noted.



➡ User Feed Direction

Orientation of Component Inside Pocket

Tape and Reel Packaging

32 mm wide by 16 mm pitch; 13 inch OD, 4 inch ID
 300 components per reel, maximum
 Meets ANSI/EIA 481-2 Carrier Tape Standards

©2001 Bel Fuse Inc. Specifications subject to change without notice. 08.01

CORPORATE

Bel Fuse Inc.
 206 Van Vorst Street
 Jersey City, NJ 07302
 Tel 201-432-0463
 Fax 201-432-9542
 www.belfuse.com

FAR EAST

Bel Fuse Ltd.
 8F / 8 Luk Hop Street
 San Po Kong
 Kowloon, Hong Kong
 Tel 852-2328-5515
 Fax 852-2352-3706
 www.belfuse.com

EUROPE

Bel Fuse Europe Ltd.
 Preston Technology Management Centre
 Marsh Lane, Suite G7, Preston
 Lancashire, PR1 8UD, U.K.
 Tel 44-1772-556601
 Fax 44-1772-888366
 www.belfuse.com